

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573169

Luminaire Tested: **FLD4C-35-D010 FEU4C-X-90-35 F4X-N-X-LI-BL84**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573169
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208279)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-35-D010 FEU4C-X-90-35 F4X-N-X-LI-BL84
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 3500K, 90 CRI LEDS, 4LBNI TRIM
AND BOTTOM LENS, 0.125" CLEAR POLYCARBONATE

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2393.0 lumens
Efficiency: N/A
Efficacy: 59.2 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 40.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573169

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-35 F4X-N-X-LI-BL84

Luminous Intensity Polar Plot





TEST NUMBER: P573169

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-35 F4X-N-X-LI-BL84

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			50
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			102
1	114	112	110	108		112	110	108	106		106	104	103			102	101	100			99
2	109	105	102	99		107	103	100	98		100	98	95			97	95	93			95
3	105	99	95	92		103	98	94	91		95	92	89			93	90	88			91
4	101	94	89	86		99	93	88	85		91	87	84			89	86	83			87
5	96	89	84	80		95	88	84	80		87	82	79			85	81	79			83
6	92	85	80	76		91	84	79	76		83	78	75			81	78	75			80
7	89	81	76	72		88	80	75	72		79	75	71			78	74	71			77
8	85	77	72	68		84	77	72	68		76	71	68			75	71	68			74
9	82	74	69	65		81	73	68	65		72	68	65			72	68	65			71
10	79	71	66	62		78	70	65	62		69	65	62			69	65	62			68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	756556
5°	680828
10°	527787
15°	382007
20°	264509
25°	192839
30°	140114
35°	82907
40°	34865
45°	10876
50°	1414
55°	792
60°	909
65°	1076
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P573169

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-35 F4X-N-X-LI-BL84

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	485.3	20.3
10°-20°	830.8	34.7
20°-30°	660.3	27.6
30°-40°	349.6	14.6
40°-50°	60.2	2.5
50°-60°	4.5	0.2
60°-70°	2.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1976.5	82.6
0°-40°	2326.0	97.2
0°-60°	2390.7	99.9
0°-90°	2393.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2393.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6158	
5°	5521	485
15°	3004	831
25°	1423	660
35°	553	350
45°	63	60
55°	4	5
65°	4	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P573169

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-35 F4X-N-X-LI-BL84

CANDELA DISTRIBUTION (FULL):

0°	
0°	6158.2
2.5°	5999.7
5°	5520.7
7.5°	4894.2
10°	4230.8
12.5°	3589.6
15°	3003.5
17.5°	2458.1
20°	2023.2
22.5°	1691.5
25°	1422.6
27.5°	1205.1
30°	987.7
32.5°	766.6
35°	552.8
37.5°	364.9
40°	217.4
42.5°	125.3
45°	62.6
47.5°	22.1
50°	7.4
52.5°	7.4
55°	3.7
57.5°	3.7
60°	3.7
62.5°	3.7
65°	3.7
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)