

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573629

Luminaire Tested: **FLD4C-50-D010 FEU4C-X-90-27 F4X-M-X-LI-BL89BV**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573629
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205108)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-50-D010 FEU4C-X-90-27 F4X-M-X-LI-BL89BV
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 2700K, 90 CRI LEDS, 4LBMLI TRIM
AND BOTTOM LENS, 0.125" CLEAR ACRYLIC

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4631.1 lumens
Efficiency: N/A
Efficacy: 79.3 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 58.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573629

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-27 F4X-M-X-LI-BL89BV

Luminous Intensity Polar Plot



TEST NUMBER: P573629

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-27 F4X-M-X-LI-BL89BV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94						
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88						
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82						
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76						
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71						
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67						
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63						
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59						
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55						
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52						

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	711997
5°	705221
10°	668266
15°	606721
20°	536130
25°	463499
30°	362308
35°	222190
40°	114042
45°	45312
50°	14717
55°	5076
60°	4349
65°	3459
70°	2155
75°	2848
80°	0
85°	0



TEST NUMBER: P573629

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-27 F4X-M-X-LI-BL89BV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	533.9	11.5
10°-20°	1329.2	28.7
20°-30°	1545.1	33.4
30°-40°	946.2	20.4
40°-50°	235.0	5.1
50°-60°	27.5	0.6
60°-70°	10.3	0.2
70°-80°	3.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3408.2	73.6
0°-40°	4354.4	94.0
0°-60°	4616.9	99.7
0°-90°	4631.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4631.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5796	
5°	5718	534
15°	4770	1329
25°	3419	1545
35°	1482	946
45°	261	235
55°	24	27
65°	12	10
75°	6	4
85°	0	0
90°	0	



TEST NUMBER: P573629

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-27 F4X-M-X-LI-BL89BV

CANDELA DISTRIBUTION (FULL):

	0°
0°	5795.5
2.5°	5789.5
5°	5718.5
7.5°	5564.3
10°	5356.9
12.5°	5084.4
15°	4770.3
17.5°	4432.5
20°	4100.8
22.5°	3768.8
25°	3419.3
27.5°	3016.3
30°	2554.0
32.5°	2014.8
35°	1481.5
37.5°	1042.9
40°	711.1
42.5°	444.4
45°	260.8
47.5°	148.2
50°	77.0
52.5°	35.6
55°	23.7
57.5°	17.7
60°	17.7
62.5°	11.9
65°	11.9
67.5°	6.0
70°	6.0
72.5°	6.0
75°	6.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)