

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573659

Luminaire Tested: **FLD4C-50-D010 FEU4C-X-90-30 F4X-M-X-H-BL89BV**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573659
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207151)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-50-D010 FEU4C-X-90-30 F4X-M-X-H-BL89BV
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 3000K, 90 CRI LEDS, 4LBMH TRIM
AND BOTTOM LENS, 0.125" CLEAR ACRYLIC

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3859.0 lumens
Efficiency: N/A
Efficacy: 66.1 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 58.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573659

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-30 F4X-M-X-H-BL89BV

Luminous Intensity Polar Plot





TEST NUMBER: P573659

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-30 F4X-M-X-H-BL89BV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	108	105		111	108	106	104		104	102	100		100	99	97		97	96	95
2	107	102	98	94		105	100	96	93		97	94	91		94	91	89		91	89	87
3	101	94	89	85		99	93	88	84		90	86	83		88	84	82		86	83	80
4	96	88	82	77		94	86	81	77		84	80	76		82	78	75		80	77	74
5	90	82	75	71		89	81	75	70		79	74	70		77	73	69		75	72	69
6	86	76	70	65		84	75	69	65		74	68	64		72	68	64		71	67	64
7	81	71	65	60		80	70	64	60		69	64	60		68	63	59		67	62	59
8	77	67	60	56		75	66	60	56		65	59	56		64	59	55		63	58	55
9	73	63	56	52		72	62	56	52		61	56	52		60	55	52		59	55	52
10	69	59	53	49		68	59	53	49		58	52	49		57	52	48		56	52	48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	470087
5°	463262
10°	443906
15°	419273
20°	391364
25°	355273
30°	296613
35°	214886
40°	134522
45°	76898
50°	40098
55°	22468
60°	14325
65°	8459
70°	6286
75°	2753
80°	4103
85°	0



TEST NUMBER: P573659

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-30 F4X-M-X-H-BL89BV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	352.1	9.1
10°-20°	923.7	23.9
20°-30°	1187.1	30.8
30°-40°	893.2	23.1
40°-50°	358.7	9.3
50°-60°	102.0	2.6
60°-70°	32.3	0.8
70°-80°	9.2	0.2
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2462.9	63.8
0°-40°	3356.1	87.0
0°-60°	3816.8	98.9
0°-90°	3859.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3859.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3826	
5°	3756	352
15°	3296	924
25°	2621	1187
35°	1433	893
45°	443	359
55°	105	102
65°	29	32
75°	6	9
85°	0	1
90°	0	



TEST NUMBER: P573659

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-30 F4X-M-X-H-BL89BV

CANDELA DISTRIBUTION (FULL):

0°	
0°	3826.4
2.5°	3803.1
5°	3756.5
7.5°	3669.1
10°	3558.4
12.5°	3424.7
15°	3296.5
17.5°	3150.8
20°	2993.5
22.5°	2824.8
25°	2620.9
27.5°	2376.2
30°	2090.9
32.5°	1770.5
35°	1432.8
37.5°	1118.2
40°	838.8
42.5°	617.3
45°	442.6
47.5°	303.0
50°	209.8
52.5°	145.7
55°	104.9
57.5°	75.7
60°	58.3
62.5°	40.8
65°	29.1
67.5°	23.3
70°	17.5
72.5°	11.7
75°	5.8
77.5°	5.8
80°	5.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)