

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573683

Luminaire Tested: **FLD4C-50-D010 FEU4C-X-90-30 F4X-W-X-H-BL89BV**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573683
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-50-D010 FEU4C-X-90-30 F4X-W-X-H-BL89BV
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 3000K, 90 CRI LEDS, 4LBWH TRIM
AND BOTTOM LENS, 0.125" CLEAR ACRYLIC

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4290.0 lumens
Efficiency: N/A
Efficacy: 73.5 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 58.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573683

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-30 F4X-W-X-H-BL89BV

Luminous Intensity Polar Plot



TEST NUMBER: P573683

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-30 F4X-W-X-H-BL89BV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91						
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82						
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74						
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67						
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61						
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55						
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50						
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46						
9	68	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43						
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39						

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	339714
5°	341012
10°	342048
15°	342057
20°	340180
25°	332215
30°	310501
35°	268893
40°	210042
45°	150703
50°	97895
55°	58602
60°	34301
65°	22035
70°	14655
75°	11060
80°	8278
85°	0



TEST NUMBER: P573683

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-30 F4X-W-X-H-BL89BV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	263.3	6.1
10°-20°	758.8	17.7
20°-30°	1119.6	26.1
30°-40°	1104.9	25.8
40°-50°	676.1	15.8
50°-60°	259.2	6.0
60°-70°	81.1	1.9
70°-80°	23.8	0.6
80°-90°	3.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2141.7	49.9
0°-40°	3246.6	75.7
0°-60°	4182.0	97.5
0°-90°	4290.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4290.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2765	
5°	2765	263
15°	2689	759
25°	2451	1120
35°	1793	1105
45°	867	676
55°	274	259
65°	76	81
75°	23	24
85°	0	3
90°	0	



TEST NUMBER: P573683

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-30 F4X-W-X-H-BL89BV

CANDELA DISTRIBUTION (FULL):

	0°
0°	2765.2
2.5°	2771.0
5°	2765.2
7.5°	2759.3
10°	2741.9
12.5°	2718.5
15°	2689.4
17.5°	2654.4
20°	2602.0
22.5°	2544.0
25°	2450.8
27.5°	2334.2
30°	2188.8
32.5°	2008.5
35°	1792.9
37.5°	1554.2
40°	1309.7
42.5°	1082.8
45°	867.4
47.5°	675.1
50°	512.2
52.5°	378.5
55°	273.6
57.5°	192.0
60°	139.6
62.5°	104.9
65°	75.8
67.5°	58.3
70°	40.8
72.5°	29.1
75°	23.3
77.5°	11.7
80°	11.7
82.5°	5.8
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)