

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573695

Luminaire Tested: **FLD4C-50-D010 FEU4C-X-90-35 F4X-M-X-H-BL89BV**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573695
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207151)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-50-D010 FEU4C-X-90-35 F4X-M-X-H-BL89BV
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 3500K, 90 CRI LEDS, 4LBMH TRIM
AND BOTTOM LENS, 0.125" CLEAR ACRYLIC

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3913.9 lumens
Efficiency: N/A
Efficacy: 67.0 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 58.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573695

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-35 F4X-M-X-H-BL89BV

Luminous Intensity Polar Plot





TEST NUMBER: P573695

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-35 F4X-M-X-H-BL89BV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	108	105		111	108	106	104		104	102	100		100	99	97		97	96	95
2	107	102	98	94		105	100	96	93		97	94	91		94	91	89		91	89	87
3	101	94	89	85		99	93	88	84		90	86	83		88	84	82		86	83	80
4	96	88	82	77		94	86	81	77		84	80	76		82	78	75		80	77	74
5	90	82	75	71		89	81	75	70		79	74	70		77	73	69		75	72	69
6	86	76	70	65		84	75	69	65		74	68	64		72	68	64		71	67	64
7	81	71	65	60		80	70	64	60		69	64	60		68	63	59		67	62	59
8	77	67	60	56		75	66	60	56		65	59	56		64	59	55		63	58	55
9	73	63	56	52		72	62	56	52		61	56	52		60	55	52		59	55	52
10	69	59	53	49		68	59	53	49		58	52	49		57	52	48		56	52	48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	476794
5°	469872
10°	450230
15°	425251
20°	396947
25°	360329
30°	300840
35°	217946
40°	136430
45°	77992
50°	40653
55°	22790
60°	14521
65°	8576
70°	6358
75°	2801
80°	4174
85°	0



TEST NUMBER: P573695

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-35 F4X-M-X-H-BL89BV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	357.1	9.1
10°-20°	936.9	23.9
20°-30°	1204.0	30.8
30°-40°	905.9	23.1
40°-50°	363.8	9.3
50°-60°	103.4	2.6
60°-70°	32.7	0.8
70°-80°	9.3	0.2
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2498.0	63.8
0°-40°	3403.9	87.0
0°-60°	3871.1	98.9
0°-90°	3913.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3913.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3881	
5°	3810	357
15°	3344	937
25°	2658	1204
35°	1453	906
45°	449	364
55°	106	103
65°	30	33
75°	6	9
85°	0	1
90°	0	



TEST NUMBER: P573695

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-35 F4X-M-X-H-BL89BV

CANDELA DISTRIBUTION (FULL):

	0°
0°	3881.0
2.5°	3857.3
5°	3810.1
7.5°	3721.4
10°	3609.1
12.5°	3473.5
15°	3343.5
17.5°	3195.7
20°	3036.2
22.5°	2865.1
25°	2658.2
27.5°	2410.0
30°	2120.7
32.5°	1795.7
35°	1453.2
37.5°	1134.1
40°	850.7
42.5°	626.1
45°	448.9
47.5°	307.3
50°	212.7
52.5°	147.7
55°	106.4
57.5°	76.8
60°	59.1
62.5°	41.4
65°	29.5
67.5°	23.6
70°	17.7
72.5°	11.8
75°	5.9
77.5°	5.9
80°	5.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)