

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573706

Luminaire Tested: **FLD4C-50-D010 FEU4C-X-90-35 F4X-N-X-H-BL89AM**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573706
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207666)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-50-D010 FEU4C-X-90-35 F4X-N-X-H-BL89AM
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 3500K, 90 CRI LEDS, 4LBNH TRIM
AND BOTTOM LENS, 0.125" OPAL POLYCARBONATE

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1341.0 lumens
Efficiency: N/A
Efficacy: 23.0 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 58.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573706

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-35 F4X-N-X-H-BL89AM

Luminous Intensity Polar Plot





TEST NUMBER: P573706

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-35 F4X-N-X-H-BL89AM

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	111	108	106		111	109	106	104		105	103	101		101	99	98		97	96	95
2	108	103	99	96		106	101	98	94		98	95	92		95	93	90		92	90	89
3	102	96	91	87		100	95	90	86		92	88	85		90	86	84		87	85	82
4	97	90	84	80		95	89	83	79		86	82	78		84	81	78		83	79	77
5	92	84	78	74		91	83	78	73		81	76	73		80	75	72		78	74	72
6	88	79	73	69		86	78	72	68		77	72	68		75	71	67		74	70	67
7	83	74	68	64		82	73	68	64		72	67	63		71	66	63		70	66	63
8	79	70	64	60		78	69	64	60		68	63	59		67	63	59		66	62	59
9	76	66	60	56		74	65	60	56		65	59	56		64	59	56		63	59	55
10	72	62	57	53		71	62	56	53		61	56	53		60	56	52		60	55	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	206848
5°	202237
10°	186998
15°	167785
20°	147708
25°	127109
30°	102365
35°	68149
40°	35443
45°	16054
50°	6957
55°	4669
60°	2998
65°	2122
70°	1760
75°	1139
80°	0
85°	0



TEST NUMBER: P573706

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-35 F4X-N-X-H-BL89AM

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	151.9	11.3
10°-20°	368.5	27.5
20°-30°	427.8	31.9
30°-40°	283.3	21.1
40°-50°	79.5	5.9
50°-60°	20.0	1.5
60°-70°	7.5	0.6
70°-80°	2.5	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	948.2	70.7
0°-40°	1231.5	91.8
0°-60°	1330.9	99.3
0°-90°	1341.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1341.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1684	
5°	1640	152
15°	1319	368
25°	938	428
35°	454	283
45°	92	79
55°	22	20
65°	7	8
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P573706

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-35 F4X-N-X-H-BL89AM

CANDELA DISTRIBUTION (FULL):

	0°
0°	1683.7
2.5°	1676.4
5°	1639.9
7.5°	1576.7
10°	1499.0
12.5°	1411.5
15°	1319.2
17.5°	1229.3
20°	1129.8
22.5°	1037.4
25°	937.7
27.5°	843.1
30°	721.6
32.5°	592.8
35°	454.4
37.5°	325.6
40°	221.0
42.5°	143.3
45°	92.4
47.5°	55.9
50°	36.4
52.5°	26.7
55°	21.8
57.5°	17.1
60°	12.2
62.5°	9.7
65°	7.3
67.5°	4.9
70°	4.9
72.5°	2.4
75°	2.4
77.5°	2.4
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)