

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573251

Luminaire Tested: **FLD4C-35-D010 FEU4C-X-90-50 F4X-W-X-H-BL89BV**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573251
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-35-D010 FEU4C-X-90-50 F4X-W-X-H-BL89BV
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 5000K, 90 CRI LEDS, 4LBWH TRIM
AND BOTTOM LENS, 0.125" CLEAR ACRYLIC

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2922.0 lumens
Efficiency: N/A
Efficacy: 72.3 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 40.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573251

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-50 F4X-W-X-H-BL89BV

Luminous Intensity Polar Plot





TEST NUMBER: P573251

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-50 F4X-W-X-H-BL89BV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	109	106	104		110	107	104	102		103	101	99		99	97	96		96	94	93
2	105	100	95	91		103	98	93	90		95	91	88		91	88	86		89	86	84
3	99	91	85	80		97	90	84	80		87	82	78		84	80	77		82	79	76
4	92	83	77	72		90	82	76	71		80	75	70		78	73	70		76	72	69
5	87	77	70	65		85	76	69	64		74	68	64		72	67	63		70	66	62
6	81	71	64	58		80	70	63	58		68	62	58		67	61	57		65	61	57
7	76	65	58	53		75	65	58	53		63	57	53		62	56	52		61	56	52
8	72	60	53	49		70	60	53	49		59	53	48		58	52	48		57	52	48
9	68	56	49	45		66	56	49	45		55	49	44		54	48	44		53	48	44
10	64	52	46	41		63	52	46	41		51	45	41		50	45	41		49	44	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	231382
5°	232266
10°	232968
15°	232982
20°	231707
25°	226280
30°	211483
35°	183136
40°	143069
45°	102646
50°	66684
55°	39925
60°	23367
65°	15000
70°	9986
75°	7547
80°	5589
85°	0



TEST NUMBER: P573251

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-50 F4X-W-X-H-BL89BV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	179.4	6.1
10°-20°	516.8	17.7
20°-30°	762.6	26.1
30°-40°	752.6	25.8
40°-50°	460.5	15.8
50°-60°	176.6	6.0
60°-70°	55.2	1.9
70°-80°	16.2	0.6
80°-90°	2.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1458.8	49.9
0°-40°	2211.3	75.7
0°-60°	2848.5	97.5
0°-90°	2922.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2922.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1883	
5°	1883	179
15°	1832	517
25°	1669	763
35°	1221	753
45°	591	461
55°	186	177
65°	52	55
75°	16	16
85°	0	2
90°	0	



TEST NUMBER: P573251

CATALOG NUMBER: FLD4C-35-D010 FEU4C-X-90-50 F4X-W-X-H-BL89BV

CANDELA DISTRIBUTION (FULL):

	0°
0°	1883.4
2.5°	1887.4
5°	1883.4
7.5°	1879.4
10°	1867.5
12.5°	1851.7
15°	1831.8
17.5°	1808.0
20°	1772.3
22.5°	1732.8
25°	1669.3
27.5°	1589.9
30°	1490.8
32.5°	1368.0
35°	1221.1
37.5°	1058.6
40°	892.1
42.5°	737.5
45°	590.8
47.5°	459.8
50°	348.9
52.5°	257.8
55°	186.4
57.5°	130.8
60°	95.1
62.5°	71.4
65°	51.6
67.5°	39.7
70°	27.8
72.5°	19.8
75°	15.9
77.5°	7.9
80°	7.9
82.5°	4.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)