

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573712

Luminaire Tested: **FLD4C-50-D010 FEU4C-X-90-35 F4X-N-X-LI-BL89AM**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573712
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208279)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-50-D010 FEU4C-X-90-35 F4X-N-X-LI-BL89AM
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 3500K, 90 CRI LEDS, 4LBNLI TRIM
AND BOTTOM LENS, 0.125" OPAL POLYCARBONATE

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1579.9 lumens
Efficiency: N/A
Efficacy: 27.1 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 58.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573712

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-35 F4X-N-X-LI-BL89AM

Luminous Intensity Polar Plot





TEST NUMBER: P573712

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-35 F4X-N-X-LI-BL89AM

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	109	105	102	99	107	103	100	98	100	98	95		97	95	93		95
3	105	99	95	92	103	98	94	91	95	92	89		93	90	88		91
4	101	94	89	86	99	93	88	85	91	87	84		89	86	83		87
5	96	89	84	80	95	88	84	80	87	82	79		85	81	79		83
6	92	85	80	76	91	84	79	76	83	78	75		81	78	75		80
7	89	81	76	72	88	80	75	72	79	75	71		78	74	71		77
8	85	77	72	68	84	77	72	68	76	71	68		75	71	68		74
9	82	74	69	65	81	73	68	65	72	68	65		72	68	65		71
10	79	71	66	62	78	70	65	62	69	65	62		69	65	62		68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	499522
5°	449524
10°	348473
15°	252225
20°	174640
25°	127326
30°	92506
35°	54741
40°	23030
45°	7176
50°	937
55°	514
60°	590
65°	698
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P573712

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-35 F4X-N-X-LI-BL89AM

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	320.4	20.3
10°-20°	548.6	34.7
20°-30°	436.0	27.6
30°-40°	230.8	14.6
40°-50°	39.7	2.5
50°-60°	3.0	0.2
60°-70°	1.5	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1305.0	82.6
0°-40°	1535.8	97.2
0°-60°	1578.5	99.9
0°-90°	1579.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1579.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4066	
5°	3645	320
15°	1983	549
25°	939	436
35°	365	231
45°	41	40
55°	2	3
65°	2	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P573712

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-35 F4X-N-X-LI-BL89AM

CANDELA DISTRIBUTION (FULL):

0°	
0°	4066.0
2.5°	3961.3
5°	3645.1
7.5°	3231.4
10°	2793.4
12.5°	2370.0
15°	1983.1
17.5°	1623.0
20°	1335.8
22.5°	1116.8
25°	939.3
27.5°	795.7
30°	652.1
32.5°	506.1
35°	365.0
37.5°	240.9
40°	143.6
42.5°	82.7
45°	41.3
47.5°	14.6
50°	4.9
52.5°	4.9
55°	2.4
57.5°	2.4
60°	2.4
62.5°	2.4
65°	2.4
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)