

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573713

Luminaire Tested: **FLD4C-50-D010 FEU4C-X-90-35 F4X-N-X-LI-BL89BV**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573713
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208279)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-50-D010 FEU4C-X-90-35 F4X-N-X-LI-BL89BV
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 3500K, 90 CRI LEDS, 4LBNLI TRIM
AND BOTTOM LENS, 0.125" CLEAR ACRYLIC

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3831.0 lumens
Efficiency: N/A
Efficacy: 65.6 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 58.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573713

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-35 F4X-N-X-LI-BL89BV

Luminous Intensity Polar Plot





TEST NUMBER: P573713

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-35 F4X-N-X-LI-BL89BV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			50
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			102
1	114	112	110	108		112	110	108	106		106	104	103			102	101	100			99
2	109	105	102	99		107	103	100	98		100	98	95			97	95	93			95
3	105	99	95	92		103	98	94	91		95	92	89			93	90	88			91
4	101	94	89	86		99	93	88	85		91	87	84			89	86	83			87
5	96	89	84	80		95	88	84	80		87	82	79			85	81	79			83
6	92	85	80	76		91	84	79	76		83	78	75			81	78	75			80
7	89	81	76	72		88	80	75	72		79	75	71			78	74	71			77
8	85	77	72	68		84	77	72	68		76	71	68			75	71	68			74
9	82	74	69	65		81	73	68	65		72	68	65			72	68	65			71
10	79	71	66	62		78	70	65	62		69	65	62			69	65	62			68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1211188
5°	1089939
10°	844948
15°	611567
20°	423460
25°	308710
30°	224307
35°	132729
40°	55826
45°	17409
50°	2255
55°	1264
60°	1450
65°	1715
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P573713

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-35 F4X-N-X-LI-BL89BV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	776.9	20.3
10°-20°	1330.1	34.7
20°-30°	1057.1	27.6
30°-40°	559.6	14.6
40°-50°	96.4	2.5
50°-60°	7.2	0.2
60°-70°	3.6	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3164.1	82.6
0°-40°	3723.8	97.2
0°-60°	3827.4	99.9
0°-90°	3831.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3831.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9859	
5°	8838	777
15°	4808	1330
25°	2277	1057
35°	885	560
45°	100	96
55°	6	7
65°	6	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P573713

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-35 F4X-N-X-LI-BL89BV

CANDELA DISTRIBUTION (FULL):

0°	
0°	9858.8
2.5°	9605.0
5°	8838.1
7.5°	7835.2
10°	6773.2
12.5°	5746.6
15°	4808.4
17.5°	3935.2
20°	3239.0
22.5°	2708.0
25°	2277.4
27.5°	1929.3
30°	1581.2
32.5°	1227.2
35°	885.0
37.5°	584.2
40°	348.1
42.5°	200.6
45°	100.2
47.5°	35.5
50°	11.8
52.5°	11.8
55°	5.9
57.5°	5.9
60°	5.9
62.5°	5.9
65°	5.9
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)