

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573370

Luminaire Tested: **FLD4C-40-D010 FEU4C-X-90-40 F4X-M-X-H-BL89AM**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573370
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207151)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-40-D010 FEU4C-X-90-40 F4X-M-X-H-BL89AM
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 4000K, 90 CRI LEDS, 4LBMH TRIM
AND BOTTOM LENS, 0.125" OPAL POLYCARBONATE

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1233.0 lumens
Efficiency: N/A
Efficacy: 26.2 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573370

CATALOG NUMBER: FLD4C-40-D010 FEU4C-X-90-40 F4X-M-X-H-BL89AM

Luminous Intensity Polar Plot





TEST NUMBER: P573370

CATALOG NUMBER: FLD4C-40-D010 FEU4C-X-90-40 F4X-M-X-H-BL89AM

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	82		86
4	96	88	82	77	94	86	81	77	84	80	76		82	78	75		80
5	90	82	75	71	89	81	75	70	79	74	70		77	73	69		75
6	86	76	70	65	84	75	69	65	74	68	64		72	68	64		71
7	81	71	65	60	80	70	64	60	69	64	60		68	63	59		67
8	77	67	60	56	75	66	60	56	65	59	56		64	59	55		63
9	73	63	56	52	72	62	56	52	61	56	52		60	55	52		59
10	69	59	53	49	68	59	53	49	58	52	49		57	52	48		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	150201
5°	148024
10°	141839
15°	133966
20°	125051
25°	113513
30°	94776
35°	68659
40°	42980
45°	24567
50°	12805
55°	7175
60°	4570
65°	2703
70°	2012
75°	902
80°	1344
85°	0



TEST NUMBER: P573370

CATALOG NUMBER: FLD4C-40-D010 FEU4C-X-90-40 F4X-M-X-H-BL89AM

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	112.5	9.1
10°-20°	295.1	23.9
20°-30°	379.3	30.8
30°-40°	285.4	23.1
40°-50°	114.6	9.3
50°-60°	32.6	2.6
60°-70°	10.3	0.8
70°-80°	3.0	0.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	786.9	63.8
0°-40°	1072.3	87.0
0°-60°	1219.5	98.9
0°-90°	1233.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1233.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1223	
5°	1200	112
15°	1053	295
25°	837	379
35°	458	285
45°	141	115
55°	34	33
65°	9	10
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P573370

CATALOG NUMBER: FLD4C-40-D010 FEU4C-X-90-40 F4X-M-X-H-BL89AM

CANDELA DISTRIBUTION (FULL):

	0°
0°	1222.6
2.5°	1215.1
5°	1200.3
7.5°	1172.3
10°	1137.0
12.5°	1094.2
15°	1053.3
17.5°	1006.7
20°	956.5
22.5°	902.6
25°	837.4
27.5°	759.2
30°	668.1
32.5°	565.7
35°	457.8
37.5°	357.3
40°	268.0
42.5°	197.3
45°	141.4
47.5°	96.8
50°	67.0
52.5°	46.5
55°	33.5
57.5°	24.2
60°	18.6
62.5°	13.0
65°	9.3
67.5°	7.4
70°	5.6
72.5°	3.7
75°	1.9
77.5°	1.9
80°	1.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)