

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573395

Luminaire Tested: **FLD4C-40-D010 FEU4C-X-90-40 F4X-W-X-H-BL89BV**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573395
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-40-D010 FEU4C-X-90-40 F4X-W-X-H-BL89BV
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 4000K, 90 CRI LEDS, 4LBWH TRIM
AND BOTTOM LENS, 0.125" CLEAR ACRYLIC

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3322.0 lumens
Efficiency: N/A
Efficacy: 70.7 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573395

CATALOG NUMBER: FLD4C-40-D010 FEU4C-X-90-40 F4X-W-X-H-BL89BV

Luminous Intensity Polar Plot





TEST NUMBER: P573395

CATALOG NUMBER: FLD4C-40-D010 FEU4C-X-90-40 F4X-W-X-H-BL89BV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96
2	105	100	95	91	103	98	93	90	95	91	88		91	88	86		89
3	99	91	85	80	97	90	84	80	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	64	74	68	64		72	67	63		70
6	81	71	64	58	80	70	63	58	68	62	58		67	61	57		65
7	76	65	58	53	75	65	58	53	63	57	53		62	56	52		61
8	72	60	53	49	70	60	53	49	59	53	48		58	52	48		57
9	68	56	49	45	66	56	49	45	55	49	44		54	48	44		53
10	64	52	46	41	63	52	46	41	51	45	41		50	45	41		49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	263054
5°	264059
10°	264866
15°	264880
20°	263424
25°	257254
30°	240437
35°	208212
40°	162651
45°	116702
50°	75820
55°	45387
60°	26561
65°	17064
70°	11351
75°	8544
80°	6367
85°	0



TEST NUMBER: P573395

CATALOG NUMBER: FLD4C-40-D010 FEU4C-X-90-40 F4X-W-X-H-BL89BV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	203.9	6.1
10°-20°	587.6	17.7
20°-30°	867.0	26.1
30°-40°	855.6	25.8
40°-50°	523.6	15.8
50°-60°	200.7	6.0
60°-70°	62.8	1.9
70°-80°	18.4	0.6
80°-90°	2.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1658.5	49.9
0°-40°	2514.1	75.7
0°-60°	3238.4	97.5
0°-90°	3322.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3322.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2141	
5°	2141	204
15°	2083	588
25°	1898	867
35°	1388	856
45°	672	524
55°	212	201
65°	59	63
75°	18	18
85°	0	2
90°	0	



TEST NUMBER: P573395

CATALOG NUMBER: FLD4C-40-D010 FEU4C-X-90-40 F4X-W-X-H-BL89BV

CANDELA DISTRIBUTION (FULL):

	0°
0°	2141.2
2.5°	2145.7
5°	2141.2
7.5°	2136.7
10°	2123.2
12.5°	2105.1
15°	2082.6
17.5°	2055.5
20°	2014.9
22.5°	1970.0
25°	1897.8
27.5°	1807.5
30°	1694.9
32.5°	1555.3
35°	1388.3
37.5°	1203.5
40°	1014.2
42.5°	838.4
45°	671.7
47.5°	522.8
50°	396.7
52.5°	293.1
55°	211.9
57.5°	148.7
60°	108.1
62.5°	81.2
65°	58.7
67.5°	45.1
70°	31.6
72.5°	22.6
75°	18.0
77.5°	9.0
80°	9.0
82.5°	4.5
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)