

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573737

Luminaire Tested: **FLD4C-50-D010 FEU4C-X-90-40 F4X-M-X-LI-BL89BV**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573737
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205108)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-50-D010 FEU4C-X-90-40 F4X-M-X-LI-BL89BV
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 4000K, 90 CRI LEDS, 4LBMLI TRIM
AND BOTTOM LENS, 0.125" CLEAR ACRYLIC

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4890.0 lumens
Efficiency: N/A
Efficacy: 83.7 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 58.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573737

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-40 F4X-M-X-LI-BL89BV

Luminous Intensity Polar Plot





TEST NUMBER: P573737

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-40 F4X-M-X-LI-BL89BV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	106	111	109	107	105	105	103	101		101	100	98		98
2	108	103	100	96	106	102	98	95	99	96	93		96	93	91		93
3	103	97	92	88	101	95	91	87	93	89	86		90	87	85		88
4	98	91	85	81	96	89	84	81	87	83	80		85	82	79		83
5	93	85	79	75	91	84	79	75	82	78	74		81	77	73		79
6	89	80	74	70	87	79	74	70	78	73	69		76	72	69		75
7	84	75	69	65	83	75	69	65	73	68	65		72	68	64		71
8	80	71	65	61	79	70	65	61	69	64	61		68	64	60		67
9	77	67	61	57	75	67	61	57	66	61	57		65	60	57		64
10	73	64	58	54	72	63	58	54	62	57	54		62	57	54		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	751814
5°	744660
10°	705641
15°	640655
20°	566108
25°	489417
30°	382579
35°	234608
40°	120425
45°	47848
50°	15539
55°	5355
60°	4595
65°	3663
70°	2263
75°	2990
80°	0
85°	0



TEST NUMBER: P573737

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-40 F4X-M-X-LI-BL89BV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	563.7	11.5
10°-20°	1403.5	28.7
20°-30°	1631.5	33.4
30°-40°	999.1	20.4
40°-50°	248.1	5.1
50°-60°	29.0	0.6
60°-70°	10.8	0.2
70°-80°	4.1	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3598.8	73.6
0°-40°	4597.9	94.0
0°-60°	4875.0	99.7
0°-90°	4890.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4890.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6120	
5°	6038	564
15°	5037	1404
25°	3610	1632
35°	1564	999
45°	275	248
55°	25	29
65°	13	11
75°	6	4
85°	0	0
90°	0	



TEST NUMBER: P573737

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-40 F4X-M-X-LI-BL89BV

CANDELA DISTRIBUTION (FULL):

	0°
0°	6119.6
2.5°	6113.3
5°	6038.3
7.5°	5875.5
10°	5656.5
12.5°	5368.7
15°	5037.1
17.5°	4680.4
20°	4330.1
22.5°	3979.5
25°	3610.5
27.5°	3185.0
30°	2696.9
32.5°	2127.4
35°	1564.3
37.5°	1101.2
40°	750.9
42.5°	469.2
45°	275.4
47.5°	156.5
50°	81.3
52.5°	37.6
55°	25.0
57.5°	18.7
60°	18.7
62.5°	12.6
65°	12.6
67.5°	6.3
70°	6.3
72.5°	6.3
75°	6.3
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)