

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573422

Luminaire Tested: **FLD4C-40-D010 FEU4C-X-90-50 F4X-N-X-LI-BL85**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573422
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208279)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-40-D010 FEU4C-X-90-50 F4X-N-X-LI-BL85
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 5000K, 90 CRI LEDS, 4LBNI TRIM
AND BOTTOM LENS, 0.187" CLEAR POLYCARBONATE

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2707.1 lumens
Efficiency: N/A
Efficacy: 57.6 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573422

CATALOG NUMBER: FLD4C-40-D010 FEU4C-X-90-50 F4X-N-X-LI-BL85

Luminous Intensity Polar Plot





TEST NUMBER: P573422

CATALOG NUMBER: FLD4C-40-D010 FEU4C-X-90-50 F4X-N-X-LI-BL85

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	110	108		112	110	108	106		106	104	103		102	101	100		99	98	97
2	109	105	102	99		107	103	100	98		100	98	95		97	95	93		95	93	92
3	105	99	95	92		103	98	94	91		95	92	89		93	90	88		91	89	87
4	101	94	89	86		99	93	88	85		91	87	84		89	86	83		87	84	82
5	96	89	84	80		95	88	84	80		87	82	79		85	81	79		83	80	78
6	92	85	80	76		91	84	79	76		83	78	75		81	78	75		80	77	74
7	89	81	76	72		88	80	75	72		79	75	71		78	74	71		77	73	71
8	85	77	72	68		84	77	72	68		76	71	68		75	71	68		74	70	67
9	82	74	69	65		81	73	68	65		72	68	65		72	68	65		71	67	64
10	79	71	66	62		78	70	65	62		69	65	62		69	65	62		68	64	62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	855834
5°	770163
10°	597047
15°	432131
20°	299220
25°	218133
30°	158499
35°	93795
40°	39452
45°	12301
50°	1605
55°	900
60°	1032
65°	1221
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P573422

CATALOG NUMBER: FLD4C-40-D010 FEU4C-X-90-50 F4X-N-X-LI-BL85

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	549.0	20.3
10°-20°	939.9	34.7
20°-30°	747.0	27.6
30°-40°	395.4	14.6
40°-50°	68.1	2.5
50°-60°	5.1	0.2
60°-70°	2.6	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2235.8	82.6
0°-40°	2631.2	97.2
0°-60°	2704.5	99.9
0°-90°	2707.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2707.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6966	
5°	6245	549
15°	3398	940
25°	1609	747
35°	625	395
45°	71	68
55°	4	5
65°	4	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P573422

CATALOG NUMBER: FLD4C-40-D010 FEU4C-X-90-50 F4X-N-X-LI-BL85

CANDELA DISTRIBUTION (FULL):

0°	
0°	6966.3
2.5°	6786.9
5°	6245.1
7.5°	5536.4
10°	4786.0
12.5°	4060.6
15°	3397.6
17.5°	2780.6
20°	2288.7
22.5°	1913.5
25°	1609.2
27.5°	1363.3
30°	1117.3
32.5°	867.2
35°	625.4
37.5°	412.8
40°	246.0
42.5°	141.8
45°	70.8
47.5°	25.1
50°	8.4
52.5°	8.4
55°	4.2
57.5°	4.2
60°	4.2
62.5°	4.2
65°	4.2
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)