

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573433

Luminaire Tested: **FLD4C-40-D010 FEU4C-X-90-50 F4X-W-X-LI-BL84**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573433
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-40-D010 FEU4C-X-90-50 F4X-W-X-LI-BL84
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 5000K, 90 CRI LEDS, 4LBWLI TRIM
AND BOTTOM LENS, 0.125" CLEAR POLYCARBONATE

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3818.0 lumens
Efficiency: N/A
Efficacy: 81.2 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573433

CATALOG NUMBER: FLD4C-40-D010 FEU4C-X-90-50 F4X-W-X-LI-BL84

Luminous Intensity Polar Plot





TEST NUMBER: P573433

CATALOG NUMBER: FLD4C-40-D010 FEU4C-X-90-50 F4X-W-X-LI-BL84

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	107	105		110	108	105	103		104	102	100		100	98	97		96	95	94
2	106	101	97	93		104	99	95	92		96	93	90		93	90	88		90	88	86
3	100	93	87	83		98	92	86	82		89	85	81		86	83	80		84	81	78
4	94	86	79	75		92	84	79	74		82	77	73		80	76	72		78	75	72
5	88	79	72	68		87	78	72	67		76	71	67		74	70	66		73	69	65
6	83	73	66	62		82	72	66	61		71	65	61		69	64	60		68	63	60
7	78	68	61	56		77	67	61	56		66	60	56		64	59	55		63	59	55
8	74	63	56	52		72	62	56	51		61	55	51		60	55	51		59	54	51
9	69	59	52	48		68	58	52	47		57	51	47		56	51	47		55	50	47
10	66	55	48	44		65	54	48	44		53	48	44		53	47	44		52	47	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	287391
5°	292263
10°	305472
15°	324226
20°	338428
25°	335496
30°	312005
35°	266913
40°	203354
45°	119291
50°	50973
55°	14993
60°	4300
65°	2558
70°	1580
75°	2089
80°	0
85°	0



TEST NUMBER: P573433

CATALOG NUMBER: FLD4C-40-D010 FEU4C-X-90-50 F4X-W-X-LI-BL84

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	228.8	6.0
10°-20°	721.9	18.9
20°-30°	1126.3	29.5
30°-40°	1095.8	28.7
40°-50°	547.3	14.3
50°-60°	84.7	2.2
60°-70°	10.3	0.3
70°-80°	2.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2077.0	54.4
0°-40°	3172.8	83.1
0°-60°	3804.9	99.7
0°-90°	3818.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3818.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2339	
5°	2370	229
15°	2549	722
25°	2475	1126
35°	1780	1096
45°	687	547
55°	70	85
65°	9	10
75°	4	3
85°	0	0
90°	0	



TEST NUMBER: P573433

CATALOG NUMBER: FLD4C-40-D010 FEU4C-X-90-50 F4X-W-X-LI-BL84

CANDELA DISTRIBUTION (FULL):

	0°
0°	2339.3
2.5°	2348.0
5°	2369.9
7.5°	2404.9
10°	2448.7
12.5°	2505.4
15°	2549.2
17.5°	2584.2
20°	2588.6
22.5°	2558.0
25°	2475.0
27.5°	2352.4
30°	2199.4
32.5°	2007.1
35°	1779.7
37.5°	1530.3
40°	1268.0
42.5°	988.2
45°	686.6
47.5°	441.6
50°	266.7
52.5°	144.3
55°	70.0
57.5°	30.6
60°	17.5
62.5°	13.1
65°	8.8
67.5°	8.8
70°	4.4
72.5°	4.4
75°	4.4
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)