

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573779

Luminaire Tested: **FLD4C-50-D010 FEU4C-X-90-50 F4X-N-X-H-BL89BV**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573779
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207666)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-50-D010 FEU4C-X-90-50 F4X-N-X-H-BL89BV
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 5000K, 90 CRI LEDS, 4LBNH TRIM
AND BOTTOM LENS, 0.125" CLEAR ACRYLIC

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3324.0 lumens
Efficiency: N/A
Efficacy: 56.9 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 58.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573779

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-50 F4X-N-X-H-BL89BV

Luminous Intensity Polar Plot





TEST NUMBER: P573779

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-50 F4X-N-X-H-BL89BV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			50
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			102
1	113	111	108	106		111	109	106	104		105	103	101			101	99	98			97
2	108	103	99	96		106	101	98	94		98	95	92			95	93	90			92
3	102	96	91	87		100	95	90	86		92	88	85			90	86	84			87
4	97	90	84	80		95	89	83	79		86	82	78			84	81	78			83
5	92	84	78	74		91	83	78	73		81	76	73			80	75	72			78
6	88	79	73	69		86	78	72	68		77	72	68			75	71	67			74
7	83	74	68	64		82	73	68	64		72	67	63			71	66	63			70
8	79	70	64	60		78	69	64	60		68	63	59			67	63	59			66
9	76	66	60	56		74	65	60	56		65	59	56			64	59	56			63
10	72	62	57	53		71	62	56	53		61	56	53			60	56	52			60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	512717
5°	501307
10°	463516
15°	415915
20°	366119
25°	315081
30°	253729
35°	168918
40°	87869
45°	39769
50°	17259
55°	11588
60°	7420
65°	5262
70°	4346
75°	2848
80°	0
85°	0



TEST NUMBER: P573779

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-50 F4X-N-X-H-BL89BV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	376.5	11.3
10°-20°	913.4	27.5
20°-30°	1060.4	31.9
30°-40°	702.3	21.1
40°-50°	197.0	5.9
50°-60°	49.5	1.5
60°-70°	18.6	0.6
70°-80°	6.3	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2350.3	70.7
0°-40°	3052.6	91.8
0°-60°	3299.1	99.2
0°-90°	3324.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3324.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4173	
5°	4065	377
15°	3270	913
25°	2324	1060
35°	1126	702
45°	229	197
55°	54	50
65°	18	19
75°	6	6
85°	0	0
90°	0	



TEST NUMBER: P573779

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-50 F4X-N-X-H-BL89BV

CANDELA DISTRIBUTION (FULL):

	0°
0°	4173.4
2.5°	4155.3
5°	4065.0
7.5°	3908.3
10°	3715.6
12.5°	3498.7
15°	3270.1
17.5°	3047.2
20°	2800.4
22.5°	2571.5
25°	2324.4
27.5°	2089.7
30°	1788.6
32.5°	1469.4
35°	1126.3
37.5°	807.0
40°	547.9
42.5°	355.2
45°	228.9
47.5°	138.6
50°	90.3
52.5°	66.2
55°	54.1
57.5°	42.3
60°	30.2
62.5°	24.2
65°	18.1
67.5°	12.1
70°	12.1
72.5°	6.0
75°	6.0
77.5°	6.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)