

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573488

Luminaire Tested: **FLD4C-45-D010 FEU4C-X-90-30 F4X-N-X-H-BL85**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573488
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207666)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-45-D010 FEU4C-X-90-30 F4X-N-X-H-BL85
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 3000K, 90 CRI LEDS, 4LBNH TRIM
AND BOTTOM LENS, 0.187" CLEAR POLYCARBONATE

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2566.0 lumens
Efficiency: N/A
Efficacy: 51.7 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 49.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573488

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-30 F4X-N-X-H-BL85

Luminous Intensity Polar Plot





TEST NUMBER: P573488

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-30 F4X-N-X-H-BL85

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	111	108	106		111	109	106	104		105	103	101		101	99	98		97	96	95
2	108	103	99	96		106	101	98	94		98	95	92		95	93	90		92	90	89
3	102	96	91	87		100	95	90	86		92	88	85		90	86	84		87	85	82
4	97	90	84	80		95	89	83	79		86	82	78		84	81	78		83	79	77
5	92	84	78	74		91	83	78	73		81	76	73		80	75	72		78	74	72
6	88	79	73	69		86	78	72	68		77	72	68		75	71	67		74	70	67
7	83	74	68	64		82	73	68	64		72	67	63		71	66	63		70	66	63
8	79	70	64	60		78	69	64	60		68	63	59		67	63	59		66	62	59
9	76	66	60	56		74	65	60	56		65	59	56		64	59	56		63	59	55
10	72	62	57	53		71	62	56	53		61	56	53		60	56	52		60	55	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	395797
5°	386987
10°	357817
15°	321072
20°	282629
25°	243238
30°	195865
35°	130389
40°	67838
45°	30700
50°	13321
55°	8932
60°	5725
65°	4070
70°	3341
75°	2231
80°	0
85°	0



TEST NUMBER: P573488

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-30 F4X-N-X-H-BL85

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	290.7	11.3
10°-20°	705.1	27.5
20°-30°	818.6	31.9
30°-40°	542.1	21.1
40°-50°	152.0	5.9
50°-60°	38.2	1.5
60°-70°	14.3	0.6
70°-80°	4.9	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1814.4	70.7
0°-40°	2356.5	91.8
0°-60°	2546.7	99.2
0°-90°	2566.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2566.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3222	
5°	3138	291
15°	2524	705
25°	1794	819
35°	869	542
45°	177	152
55°	42	38
65°	14	14
75°	5	5
85°	0	0
90°	0	



TEST NUMBER: P573488

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-30 F4X-N-X-H-BL85

CANDELA DISTRIBUTION (FULL):

	0°
0°	3221.7
2.5°	3207.7
5°	3138.0
7.5°	3017.0
10°	2868.3
12.5°	2700.9
15°	2524.4
17.5°	2352.3
20°	2161.8
22.5°	1985.1
25°	1794.4
27.5°	1613.2
30°	1380.7
32.5°	1134.3
35°	869.4
37.5°	623.0
40°	423.0
42.5°	274.2
45°	176.7
47.5°	107.0
50°	69.7
52.5°	51.1
55°	41.7
57.5°	32.6
60°	23.3
62.5°	18.6
65°	14.0
67.5°	9.3
70°	9.3
72.5°	4.7
75°	4.7
77.5°	4.7
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)