

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573505

Luminaire Tested: **FLD4C-45-D010 FEU4C-X-90-30 F4X-W-X-LI-BL84**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573505
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-45-D010 FEU4C-X-90-30 F4X-W-X-LI-BL84
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 3000K, 90 CRI LEDS, 4LBWLI TRIM
AND BOTTOM LENS, 0.125" CLEAR POLYCARBONATE

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4265.0 lumens
Efficiency: N/A
Efficacy: 86.0 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 49.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573505

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-30 F4X-W-X-LI-BL84

Luminous Intensity Polar Plot





TEST NUMBER: P573505

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-30 F4X-W-X-LI-BL84

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			50
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			102
1	113	110	107	105		110	108	105	103		104	102	100			100	98	97			96
2	106	101	97	93		104	99	95	92		96	93	90			93	90	88			90
3	100	93	87	83		98	92	86	82		89	85	81			86	83	80			84
4	94	86	79	75		92	84	79	74		82	77	73			80	76	72			78
5	88	79	72	68		87	78	72	67		76	71	67			74	70	66			73
6	83	73	66	62		82	72	66	61		71	65	61			69	64	60			68
7	78	68	61	56		77	67	61	56		66	60	56			64	59	55			63
8	74	63	56	52		72	62	56	51		61	55	51			60	55	51			59
9	69	59	52	48		68	58	52	47		57	51	47			56	51	47			55
10	66	55	48	44		65	54	48	44		53	48	44			53	47	44			52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	321028
5°	326485
10°	341238
15°	362191
20°	378055
25°	374779
30°	348533
35°	298153
40°	227170
45°	133242
50°	56936
55°	16750
60°	4816
65°	2849
70°	1760
75°	2326
80°	0
85°	0



TEST NUMBER: P573505

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-30 F4X-W-X-LI-BL84

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	255.5	6.0
10°-20°	806.5	18.9
20°-30°	1258.1	29.5
30°-40°	1224.1	28.7
40°-50°	611.4	14.3
50°-60°	94.7	2.2
60°-70°	11.5	0.3
70°-80°	3.2	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2320.2	54.4
0°-40°	3544.3	83.1
0°-60°	4250.3	99.7
0°-90°	4265.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4265.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2613	
5°	2647	256
15°	2848	806
25°	2765	1258
35°	1988	1224
45°	767	611
55°	78	95
65°	10	11
75°	5	3
85°	0	0
90°	0	



TEST NUMBER: P573505

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-30 F4X-W-X-LI-BL84

CANDELA DISTRIBUTION (FULL):

	0°
0°	2613.1
2.5°	2622.9
5°	2647.4
7.5°	2686.5
10°	2735.4
12.5°	2798.8
15°	2847.7
17.5°	2886.8
20°	2891.7
22.5°	2857.5
25°	2764.8
27.5°	2627.8
30°	2456.9
32.5°	2242.1
35°	1988.0
37.5°	1709.5
40°	1416.5
42.5°	1103.9
45°	766.9
47.5°	493.3
50°	297.9
52.5°	161.2
55°	78.2
57.5°	34.2
60°	19.6
62.5°	14.7
65°	9.8
67.5°	9.8
70°	4.9
72.5°	4.9
75°	4.9
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)