

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573506

Luminaire Tested: **FLD4C-45-D010 FEU4C-X-90-30 F4X-W-X-LI-BL85**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573506
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-45-D010 FEU4C-X-90-30 F4X-W-X-LI-BL85
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 3000K, 90 CRI LEDS, 4LBWLI TRIM
AND BOTTOM LENS, 0.187" CLEAR POLYCARBONATE

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4067.0 lumens
Efficiency: N/A
Efficacy: 82.0 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 49.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573506

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-30 F4X-W-X-LI-BL85

Luminous Intensity Polar Plot





TEST NUMBER: P573506

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-30 F4X-W-X-LI-BL85

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	107	105		110	108	105	103		104	102	100		100	98	97		96	95	94
2	106	101	97	93		104	99	95	92		96	93	90		93	90	88		90	88	86
3	100	93	87	83		98	92	86	82		89	85	81		86	83	80		84	81	78
4	94	86	79	75		92	84	79	74		82	77	73		80	76	72		78	75	72
5	88	79	72	68		87	78	72	67		76	71	67		74	70	66		73	69	65
6	83	73	66	62		82	72	66	61		71	65	61		69	64	60		68	63	60
7	78	68	61	56		77	67	61	56		66	60	56		64	59	55		63	59	55
8	74	63	56	52		72	62	56	51		61	55	51		60	55	51		59	54	51
9	69	59	52	48		68	58	52	47		57	51	47		56	51	47		55	50	47
10	66	55	48	44		65	54	48	44		53	48	44		53	47	44		52	47	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	306126
5°	311328
10°	325394
15°	345377
20°	360497
25°	357374
30°	332347
35°	284310
40°	216617
45°	127057
50°	54299
55°	15978
60°	4595
65°	2703
70°	1688
75°	2231
80°	0
85°	0



TEST NUMBER: P573506

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-30 F4X-W-X-LI-BL85

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	243.7	6.0
10°-20°	769.0	18.9
20°-30°	1199.7	29.5
30°-40°	1167.3	28.7
40°-50°	583.0	14.3
50°-60°	90.3	2.2
60°-70°	10.9	0.3
70°-80°	3.1	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2212.4	54.4
0°-40°	3379.7	83.1
0°-60°	4053.0	99.7
0°-90°	4067.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4067.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2492	
5°	2524	244
15°	2716	769
25°	2636	1200
35°	1896	1167
45°	731	583
55°	75	90
65°	9	11
75°	5	3
85°	0	0
90°	0	



TEST NUMBER: P573506

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-30 F4X-W-X-LI-BL85

CANDELA DISTRIBUTION (FULL):

	0°
0°	2491.8
2.5°	2501.2
5°	2524.5
7.5°	2561.8
10°	2608.4
12.5°	2668.8
15°	2715.5
17.5°	2752.8
20°	2757.4
22.5°	2724.8
25°	2636.4
27.5°	2505.8
30°	2342.8
32.5°	2138.0
35°	1895.7
37.5°	1630.1
40°	1350.7
42.5°	1052.7
45°	731.3
47.5°	470.4
50°	284.1
52.5°	153.7
55°	74.6
57.5°	32.6
60°	18.7
62.5°	14.0
65°	9.3
67.5°	9.3
70°	4.7
72.5°	4.7
75°	4.7
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)