

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573507

Luminaire Tested: **FLD4C-45-D010 FEU4C-X-90-30 F4X-W-X-LI-BL86**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573507
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-45-D010 FEU4C-X-90-30 F4X-W-X-LI-BL86
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 3000K, 90 CRI LEDS, 4LBWLI TRIM
AND BOTTOM LENS, 0.250" CLEAR POLYCARBONATE

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4123.0 lumens
Efficiency: N/A
Efficacy: 83.1 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 49.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573507

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-30 F4X-W-X-LI-BL86

Luminous Intensity Polar Plot





TEST NUMBER: P573507

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-30 F4X-W-X-LI-BL86

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90
3	100	93	87	83	98	92	86	82	89	85	81		86	83	80		84
4	94	86	79	75	92	84	79	74	82	77	73		80	76	72		78
5	88	79	72	68	87	78	72	67	76	71	67		74	70	66		73
6	83	73	66	62	82	72	66	61	71	65	61		69	64	60		68
7	78	68	61	56	77	67	61	56	66	60	56		64	59	55		63
8	74	63	56	52	72	62	56	51	61	55	51		60	55	51		59
9	69	59	52	48	68	58	52	47	57	51	47		56	51	47		55
10	66	55	48	44	65	54	48	44	53	48	44		53	47	44		52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	310340
5°	315608
10°	329873
15°	350134
20°	365465
25°	362295
30°	336929
35°	288225
40°	219600
45°	128812
50°	55044
55°	16193
60°	4644
65°	2762
70°	1688
75°	2231
80°	0
85°	0



TEST NUMBER: P573507

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-30 F4X-W-X-LI-BL86

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	247.0	6.0
10°-20°	779.6	18.9
20°-30°	1216.2	29.5
30°-40°	1183.4	28.7
40°-50°	591.1	14.3
50°-60°	91.5	2.2
60°-70°	11.1	0.3
70°-80°	3.1	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2242.9	54.4
0°-40°	3426.3	83.1
0°-60°	4108.8	99.7
0°-90°	4123.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4123.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2526	
5°	2559	247
15°	2753	780
25°	2673	1216
35°	1922	1183
45°	741	591
55°	76	92
65°	10	11
75°	5	3
85°	0	0
90°	0	



TEST NUMBER: P573507

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-30 F4X-W-X-LI-BL86

CANDELA DISTRIBUTION (FULL):

	0°
0°	2526.1
2.5°	2535.6
5°	2559.2
7.5°	2597.1
10°	2644.3
12.5°	2705.6
15°	2752.9
17.5°	2790.7
20°	2795.4
22.5°	2762.3
25°	2672.7
27.5°	2540.3
30°	2375.1
32.5°	2167.5
35°	1921.8
37.5°	1652.6
40°	1369.3
42.5°	1067.2
45°	741.4
47.5°	476.9
50°	288.0
52.5°	155.8
55°	75.6
57.5°	33.1
60°	18.9
62.5°	14.2
65°	9.5
67.5°	9.5
70°	4.7
72.5°	4.7
75°	4.7
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)