

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573551

Luminaire Tested: **FLD4C-45-D010 FEU4C-X-90-40 F4X-M-X-H-BL89BV**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573551
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207151)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-45-D010 FEU4C-X-90-40 F4X-M-X-H-BL89BV
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 4000K, 90 CRI LEDS, 4LBMH TRIM
AND BOTTOM LENS, 0.125" CLEAR ACRYLIC

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3460.0 lumens
Efficiency: N/A
Efficacy: 69.8 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 49.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573551

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-40 F4X-M-X-H-BL89BV

Luminous Intensity Polar Plot





TEST NUMBER: P573551

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-40 F4X-M-X-H-BL89BV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	108	105		111	108	106	104		104	102	100		100	99	97		97	96	95
2	107	102	98	94		105	100	96	93		97	94	91		94	91	89		91	89	87
3	101	94	89	85		99	93	88	84		90	86	83		88	84	82		86	83	80
4	96	88	82	77		94	86	81	77		84	80	76		82	78	75		80	77	74
5	90	82	75	71		89	81	75	70		79	74	70		77	73	69		75	72	69
6	86	76	70	65		84	75	69	65		74	68	64		72	68	64		71	67	64
7	81	71	65	60		80	70	64	60		69	64	60		68	63	59		67	62	59
8	77	67	60	56		75	66	60	56		65	59	56		64	59	55		63	58	55
9	73	63	56	52		72	62	56	52		61	56	52		60	55	52		59	55	52
10	69	59	53	49		68	59	53	49		58	52	49		57	52	48		56	52	48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	421486
5°	415363
10°	398011
15°	375915
20°	350901
25°	318538
30°	265943
35°	192675
40°	120601
45°	68940
50°	35951
55°	20134
60°	12826
65°	7587
70°	5639
75°	2468
80°	3679
85°	0



TEST NUMBER: P573551

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-40 F4X-M-X-H-BL89BV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	315.7	9.1
10°-20°	828.2	23.9
20°-30°	1064.4	30.8
30°-40°	800.8	23.1
40°-50°	321.6	9.3
50°-60°	91.4	2.6
60°-70°	29.0	0.8
70°-80°	8.2	0.2
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2208.2	63.8
0°-40°	3009.0	87.0
0°-60°	3422.1	98.9
0°-90°	3460.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3460.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3431	
5°	3368	316
15°	2956	828
25°	2350	1064
35°	1285	801
45°	397	322
55°	94	91
65°	26	29
75°	5	8
85°	0	1
90°	0	



TEST NUMBER: P573551

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-40 F4X-M-X-H-BL89BV

CANDELA DISTRIBUTION (FULL):

	0°
0°	3430.8
2.5°	3409.9
5°	3368.1
7.5°	3289.8
10°	3190.5
12.5°	3070.6
15°	2955.6
17.5°	2825.0
20°	2684.0
22.5°	2532.7
25°	2349.9
27.5°	2130.5
30°	1874.7
32.5°	1587.4
35°	1284.7
37.5°	1002.6
40°	752.0
42.5°	553.5
45°	396.8
47.5°	271.7
50°	188.1
52.5°	130.6
55°	94.0
57.5°	67.9
60°	52.2
62.5°	36.6
65°	26.1
67.5°	20.9
70°	15.7
72.5°	10.4
75°	5.2
77.5°	5.2
80°	5.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)