

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573560

Luminaire Tested: **FLD4C-45-D010 FEU4C-X-90-40 F4X-N-X-H-BL85**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573560
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207666)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-45-D010 FEU4C-X-90-40 F4X-N-X-H-BL85
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 4000K, 90 CRI LEDS, 4LBNH TRIM
AND BOTTOM LENS, 0.187" CLEAR POLYCARBONATE

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2607.0 lumens
Efficiency: N/A
Efficacy: 52.6 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 49.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573560

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-40 F4X-N-X-H-BL85

Luminous Intensity Polar Plot





TEST NUMBER: P573560

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-40 F4X-N-X-H-BL85

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	111	108	106		111	109	106	104		105	103	101		101	99	98		97	96	95
2	108	103	99	96		106	101	98	94		98	95	92		95	93	90		92	90	89
3	102	96	91	87		100	95	90	86		92	88	85		90	86	84		87	85	82
4	97	90	84	80		95	89	83	79		86	82	78		84	81	78		83	79	77
5	92	84	78	74		91	83	78	73		81	76	73		80	75	72		78	74	72
6	88	79	73	69		86	78	72	68		77	72	68		75	71	67		74	70	67
7	83	74	68	64		82	73	68	64		72	67	63		71	66	63		70	66	63
8	79	70	64	60		78	69	64	60		68	63	59		67	63	59		66	62	59
9	76	66	60	56		74	65	60	56		65	59	56		64	59	56		63	59	55
10	72	62	57	53		71	62	56	53		61	56	53		60	56	52		60	55	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	402124
5°	393178
10°	363530
15°	326197
20°	287140
25°	247115
30°	199000
35°	132474
40°	68913
45°	31187
50°	13532
55°	9082
60°	5823
65°	4128
70°	3412
75°	2231
80°	0
85°	0



TEST NUMBER: P573560

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-40 F4X-N-X-H-BL85

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	295.3	11.3
10°-20°	716.3	27.5
20°-30°	831.7	31.9
30°-40°	550.8	21.1
40°-50°	154.5	5.9
50°-60°	38.8	1.5
60°-70°	14.6	0.6
70°-80°	5.0	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1843.4	70.7
0°-40°	2394.1	91.8
0°-60°	2587.4	99.2
0°-90°	2607.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2607.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3273	
5°	3188	295
15°	2565	716
25°	1823	832
35°	883	551
45°	180	154
55°	42	39
65°	14	15
75°	5	5
85°	0	0
90°	0	



TEST NUMBER: P573560

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-40 F4X-N-X-H-BL85

CANDELA DISTRIBUTION (FULL):

	0°
0°	3273.2
2.5°	3259.0
5°	3188.2
7.5°	3065.2
10°	2914.1
12.5°	2744.0
15°	2564.7
17.5°	2389.9
20°	2196.3
22.5°	2016.8
25°	1823.0
27.5°	1639.0
30°	1402.8
32.5°	1152.4
35°	883.3
37.5°	632.9
40°	429.7
42.5°	278.6
45°	179.5
47.5°	108.7
50°	70.8
52.5°	51.9
55°	42.4
57.5°	33.2
60°	23.7
62.5°	18.9
65°	14.2
67.5°	9.5
70°	9.5
72.5°	4.7
75°	4.7
77.5°	4.7
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)