

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573614

Luminaire Tested: **FLD4C-45-D010 FEU4C-X-90-50 F4X-W-X-LI-BL85**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573614
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-45-D010 FEU4C-X-90-50 F4X-W-X-LI-BL85
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 5000K, 90 CRI LEDS, 4LBWLI TRIM
AND BOTTOM LENS, 0.187" CLEAR POLYCARBONATE

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4215.0 lumens
Efficiency: N/A
Efficacy: 85.0 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 49.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573614

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-50 F4X-W-X-LI-BL85

Luminous Intensity Polar Plot





TEST NUMBER: P573614

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-50 F4X-W-X-LI-BL85

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	107	105		110	108	105	103		104	102	100		100	98	97		96	95	94
2	106	101	97	93		104	99	95	92		96	93	90		93	90	88		90	88	86
3	100	93	87	83		98	92	86	82		89	85	81		86	83	80		84	81	78
4	94	86	79	75		92	84	79	74		82	77	73		80	76	72		78	75	72
5	88	79	72	68		87	78	72	67		76	71	67		74	70	66		73	69	65
6	83	73	66	62		82	72	66	61		71	65	61		69	64	60		68	63	60
7	78	68	61	56		77	67	61	56		66	60	56		64	59	55		63	59	55
8	74	63	56	52		72	62	56	51		61	55	51		60	55	51		59	54	51
9	69	59	52	48		68	58	52	47		57	51	47		56	51	47		55	50	47
10	66	55	48	44		65	54	48	44		53	48	44		53	47	44		52	47	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	317269
5°	322649
10°	337233
15°	357943
20°	373623
25°	370374
30°	344448
35°	294659
40°	224507
45°	131678
50°	56268
55°	16557
60°	4742
65°	2820
70°	1724
75°	2278
80°	0
85°	0



TEST NUMBER: P573614

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-50 F4X-W-X-LI-BL85

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	252.6	6.0
10°-20°	797.0	18.9
20°-30°	1243.4	29.5
30°-40°	1209.8	28.7
40°-50°	604.2	14.3
50°-60°	93.5	2.2
60°-70°	11.3	0.3
70°-80°	3.1	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2292.9	54.4
0°-40°	3502.7	83.1
0°-60°	4200.5	99.7
0°-90°	4215.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4215.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2582	
5°	2616	253
15°	2814	797
25°	2732	1243
35°	1965	1210
45°	758	604
55°	77	94
65°	10	11
75°	5	3
85°	0	0
90°	0	



TEST NUMBER: P573614

CATALOG NUMBER: FLD4C-45-D010 FEU4C-X-90-50 F4X-W-X-LI-BL85

CANDELA DISTRIBUTION (FULL):

	0°
0°	2582.5
2.5°	2592.2
5°	2616.3
7.5°	2655.0
10°	2703.3
12.5°	2766.0
15°	2814.3
17.5°	2853.0
20°	2857.8
22.5°	2824.0
25°	2732.3
27.5°	2597.0
30°	2428.1
32.5°	2215.8
35°	1964.7
37.5°	1689.5
40°	1399.9
42.5°	1091.0
45°	757.9
47.5°	487.5
50°	294.4
52.5°	159.3
55°	77.3
57.5°	33.8
60°	19.3
62.5°	14.5
65°	9.7
67.5°	9.7
70°	4.8
72.5°	4.8
75°	4.8
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)