

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573641

Luminaire Tested: **FLD4C-50-D010 FEU4C-X-90-27 F4X-N-X-LI-BL89BV**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573641
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208279)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-50-D010 FEU4C-X-90-27 F4X-N-X-LI-BL89BV
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 2700K, 90 CRI LEDS, 4LBNLI TRIM
AND BOTTOM LENS, 0.125" CLEAR ACRYLIC

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3635.0 lumens
Efficiency: N/A
Efficacy: 62.2 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 58.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573641

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-27 F4X-N-X-LI-BL89BV

Luminous Intensity Polar Plot





TEST NUMBER: P573641

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-27 F4X-N-X-LI-BL89BV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	110	108		112	110	108	106		106	104	103		102	101	100		99	98	97
2	109	105	102	99		107	103	100	98		100	98	95		97	95	93		95	93	92
3	105	99	95	92		103	98	94	91		95	92	89		93	90	88		91	89	87
4	101	94	89	86		99	93	88	85		91	87	84		89	86	83		87	84	82
5	96	89	84	80		95	88	84	80		87	82	79		85	81	79		83	80	78
6	92	85	80	76		91	84	79	76		83	78	75		81	78	75		80	77	74
7	89	81	76	72		88	80	75	72		79	75	71		78	74	71		77	73	71
8	85	77	72	68		84	77	72	68		76	71	68		75	71	68		74	70	67
9	82	74	69	65		81	73	68	65		72	68	65		72	68	65		71	67	64
10	79	71	66	62		78	70	65	62		69	65	62		69	65	62		68	64	62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1149221
5°	1034185
10°	801710
15°	580279
20°	401797
25°	292918
30°	212831
35°	125935
40°	52971
45°	16523
50°	2141
55°	1199
60°	1376
65°	1628
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P573641

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-27 F4X-N-X-LI-BL89BV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	737.2	20.3
10°-20°	1262.1	34.7
20°-30°	1003.0	27.6
30°-40°	531.0	14.6
40°-50°	91.5	2.5
50°-60°	6.8	0.2
60°-70°	3.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3002.3	82.6
0°-40°	3533.2	97.2
0°-60°	3631.5	99.9
0°-90°	3635.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3635.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9354	
5°	8386	737
15°	4562	1262
25°	2161	1003
35°	840	531
45°	95	91
55°	6	7
65°	6	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P573641

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-27 F4X-N-X-LI-BL89BV

CANDELA DISTRIBUTION (FULL):

	0°
0°	9354.4
2.5°	9113.6
5°	8386.0
7.5°	7434.3
10°	6426.6
12.5°	5452.6
15°	4562.4
17.5°	3733.9
20°	3073.3
22.5°	2569.4
25°	2160.9
27.5°	1830.6
30°	1500.3
32.5°	1164.4
35°	839.7
37.5°	554.3
40°	330.3
42.5°	190.4
45°	95.1
47.5°	33.6
50°	11.2
52.5°	11.2
55°	5.6
57.5°	5.6
60°	5.6
62.5°	5.6
65°	5.6
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)