

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573653

Luminaire Tested: **FLD4C-50-D010 FEU4C-X-90-27 F4X-W-X-LI-BL89BV**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573653
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-50-D010 FEU4C-X-90-27 F4X-W-X-LI-BL89BV
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 2700K, 90 CRI LEDS, 4LBWLI TRIM
AND BOTTOM LENS, 0.125" CLEAR ACRYLIC

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4888.0 lumens
Efficiency: N/A
Efficacy: 83.7 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 58.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573653

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-27 F4X-W-X-LI-BL89BV

Luminous Intensity Polar Plot





TEST NUMBER: P573653

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-27 F4X-W-X-LI-BL89BV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	107	105		110	108	105	103		104	102	100		100	98	97		96	95	94
2	106	101	97	93		104	99	95	92		96	93	90		93	90	88		90	88	86
3	100	93	87	83		98	92	86	82		89	85	81		86	83	80		84	81	78
4	94	86	79	75		92	84	79	74		82	77	73		80	76	72		78	75	72
5	88	79	72	68		87	78	72	67		76	71	67		74	70	66		73	69	65
6	83	73	66	62		82	72	66	61		71	65	61		69	64	60		68	63	60
7	78	68	61	56		77	67	61	56		66	60	56		64	59	55		63	59	55
8	74	63	56	52		72	62	56	51		61	55	51		60	55	51		59	54	51
9	69	59	52	48		68	58	52	47		57	51	47		56	51	47		55	50	47
10	66	55	48	44		65	54	48	44		53	48	44		53	47	44		52	47	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	367934
5°	374174
10°	391087
15°	415088
20°	433279
25°	429516
30°	399432
35°	341706
40°	260351
45°	152718
50°	65250
55°	19213
60°	5504
65°	3256
70°	2012
75°	2658
80°	0
85°	0



TEST NUMBER: P573653

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-27 F4X-W-X-LI-BL89BV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	292.9	6.0
10°-20°	924.3	18.9
20°-30°	1441.9	29.5
30°-40°	1402.9	28.7
40°-50°	700.7	14.3
50°-60°	108.5	2.2
60°-70°	13.1	0.3
70°-80°	3.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2659.0	54.4
0°-40°	4062.0	83.1
0°-60°	4871.2	99.7
0°-90°	4888.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4888.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2995	
5°	3034	293
15°	3264	924
25°	3169	1442
35°	2278	1403
45°	879	701
55°	90	108
65°	11	13
75°	6	4
85°	0	0
90°	0	



TEST NUMBER: P573653

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-27 F4X-W-X-LI-BL89BV

CANDELA DISTRIBUTION (FULL):

0°	
0°	2994.9
2.5°	3006.1
5°	3034.1
7.5°	3078.9
10°	3135.0
12.5°	3207.6
15°	3263.6
17.5°	3308.5
20°	3314.1
22.5°	3274.8
25°	3168.6
27.5°	3011.7
30°	2815.7
32.5°	2569.6
35°	2278.4
37.5°	1959.2
40°	1623.4
42.5°	1265.2
45°	879.0
47.5°	565.3
50°	341.4
52.5°	184.7
55°	89.7
57.5°	39.2
60°	22.4
62.5°	16.8
65°	11.2
67.5°	11.2
70°	5.6
72.5°	5.6
75°	5.6
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)