

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573669

Luminaire Tested: **FLD4C-50-D010 FEU4C-X-90-30 F4X-N-X-H-BL86**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573669
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207666)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-50-D010 FEU4C-X-90-30 F4X-N-X-H-BL86
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 3000K, 90 CRI LEDS, 4LBNH TRIM
AND BOTTOM LENS, 0.250" CLEAR POLYCARBONATE

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2948.0 lumens
Efficiency: N/A
Efficacy: 50.5 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 58.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573669

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-30 F4X-N-X-H-BL86

Luminous Intensity Polar Plot





TEST NUMBER: P573669

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-30 F4X-N-X-H-BL86

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	94	98	95	92		95	93	90		92
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87
4	97	90	84	80	95	89	83	79	86	82	78		84	81	78		83
5	92	84	78	74	91	83	78	73	81	76	73		80	75	72		78
6	88	79	73	69	86	78	72	68	77	72	68		75	71	67		74
7	83	74	68	64	82	73	68	64	72	67	63		71	66	63		70
8	79	70	64	60	78	69	64	60	68	63	59		67	63	59		66
9	76	66	60	56	74	65	60	56	65	59	56		64	59	56		63
10	72	62	57	53	71	62	56	53	61	56	53		60	56	52		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	454718
5°	444603
10°	411084
15°	368869
20°	324701
25°	279444
30°	225031
35°	149811
40°	77926
45°	35269
50°	15309
55°	10281
60°	6585
65°	4680
70°	3843
75°	2563
80°	0
85°	0



TEST NUMBER: P573669

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-30 F4X-N-X-H-BL86

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	333.9	11.3
10°-20°	810.1	27.5
20°-30°	940.5	31.9
30°-40°	622.8	21.1
40°-50°	174.7	5.9
50°-60°	43.9	1.5
60°-70°	16.5	0.6
70°-80°	5.7	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2084.5	70.7
0°-40°	2707.3	91.8
0°-60°	2925.9	99.2
0°-90°	2948.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2948.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3701	
5°	3605	334
15°	2900	810
25°	2062	940
35°	999	623
45°	203	175
55°	48	44
65°	16	16
75°	5	6
85°	0	0
90°	0	



TEST NUMBER: P573669

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-30 F4X-N-X-H-BL86

CANDELA DISTRIBUTION (FULL):

	0°
0°	3701.3
2.5°	3685.3
5°	3605.2
7.5°	3466.2
10°	3295.3
12.5°	3103.0
15°	2900.2
17.5°	2702.5
20°	2483.6
22.5°	2280.6
25°	2061.5
27.5°	1853.3
30°	1586.3
32.5°	1303.2
35°	998.9
37.5°	715.7
40°	485.9
42.5°	315.0
45°	203.0
47.5°	122.9
50°	80.1
52.5°	58.7
55°	48.0
57.5°	37.5
60°	26.8
62.5°	21.4
65°	16.1
67.5°	10.7
70°	10.7
72.5°	5.4
75°	5.4
77.5°	5.4
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)