

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573670

Luminaire Tested: **FLD4C-50-D010 FEU4C-X-90-30 F4X-N-X-H-BL89AM**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573670
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207666)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-50-D010 FEU4C-X-90-30 F4X-N-X-H-BL89AM
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 3000K, 90 CRI LEDS, 4LBNH TRIM
AND BOTTOM LENS, 0.125" OPAL POLYCARBONATE

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1323.0 lumens
Efficiency: N/A
Efficacy: 22.7 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 58.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573670

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-30 F4X-N-X-H-BL89AM

Luminous Intensity Polar Plot





TEST NUMBER: P573670

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-30 F4X-N-X-H-BL89AM

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	111	108	106		111	109	106	104		105	103	101		101	99	98		97	96	95
2	108	103	99	96		106	101	98	94		98	95	92		95	93	90		92	90	89
3	102	96	91	87		100	95	90	86		92	88	85		90	86	84		87	85	82
4	97	90	84	80		95	89	83	79		86	82	78		84	81	78		83	79	77
5	92	84	78	74		91	83	78	73		81	76	73		80	75	72		78	74	72
6	88	79	73	69		86	78	72	68		77	72	68		75	71	67		74	70	67
7	83	74	68	64		82	73	68	64		72	67	63		71	66	63		70	66	63
8	79	70	64	60		78	69	64	60		68	63	59		67	63	59		66	62	59
9	76	66	60	56		74	65	60	56		65	59	56		64	59	56		63	59	55
10	72	62	57	53		71	62	56	53		61	56	53		60	56	52		60	55	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	204072
5°	199524
10°	184478
15°	165534
20°	145721
25°	125414
30°	100989
35°	67234
40°	34978
45°	15828
50°	6861
55°	4605
60°	2948
65°	2093
70°	1724
75°	1139
80°	0
85°	0



TEST NUMBER: P573670

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-30 F4X-N-X-H-BL89AM

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.9	11.3
10°-20°	363.5	27.5
20°-30°	422.1	31.9
30°-40°	279.5	21.1
40°-50°	78.4	5.9
50°-60°	19.7	1.5
60°-70°	7.4	0.6
70°-80°	2.5	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	935.5	70.7
0°-40°	1215.0	91.8
0°-60°	1313.0	99.3
0°-90°	1323.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1323.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1661	
5°	1618	150
15°	1302	364
25°	925	422
35°	448	280
45°	91	78
55°	22	20
65°	7	7
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P573670

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-30 F4X-N-X-H-BL89AM

CANDELA DISTRIBUTION (FULL):

	0°
0°	1661.1
2.5°	1653.9
5°	1617.9
7.5°	1555.5
10°	1478.8
12.5°	1392.5
15°	1301.5
17.5°	1212.8
20°	1114.6
22.5°	1023.5
25°	925.2
27.5°	831.7
30°	711.9
32.5°	584.8
35°	448.3
37.5°	321.2
40°	218.1
42.5°	141.4
45°	91.1
47.5°	55.2
50°	35.9
52.5°	26.3
55°	21.5
57.5°	16.8
60°	12.0
62.5°	9.6
65°	7.2
67.5°	4.8
70°	4.8
72.5°	2.4
75°	2.4
77.5°	2.4
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)