

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573671

Luminaire Tested: **FLD4C-50-D010 FEU4C-X-90-30 F4X-N-X-H-BL89BV**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573671
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207666)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-50-D010 FEU4C-X-90-30 F4X-N-X-H-BL89BV
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 3000K, 90 CRI LEDS, 4LBNH TRIM
AND BOTTOM LENS, 0.125" CLEAR ACRYLIC

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3208.0 lumens
Efficiency: N/A
Efficacy: 54.9 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 58.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573671

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-30 F4X-N-X-H-BL89BV

Luminous Intensity Polar Plot





TEST NUMBER: P573671

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-30 F4X-N-X-H-BL89BV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	111	108	106		111	109	106	104		105	103	101		101	99	98		97	96	95
2	108	103	99	96		106	101	98	94		98	95	92		95	93	90		92	90	89
3	102	96	91	87		100	95	90	86		92	88	85		90	86	84		87	85	82
4	97	90	84	80		95	89	83	79		86	82	78		84	81	78		83	79	77
5	92	84	78	74		91	83	78	73		81	76	73		80	75	72		78	74	72
6	88	79	73	69		86	78	72	68		77	72	68		75	71	67		74	70	67
7	83	74	68	64		82	73	68	64		72	67	63		71	66	63		70	66	63
8	79	70	64	60		78	69	64	60		68	63	59		67	63	59		66	62	59
9	76	66	60	56		74	65	60	56		65	59	56		64	59	56		63	59	55
10	72	62	57	53		71	62	56	53		61	56	53		60	56	52		60	55	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	494829
5°	483808
10°	447336
15°	401390
20°	353345
25°	304088
30°	244877
35°	163009
40°	84806
45°	38379
50°	16666
55°	11181
60°	7150
65°	5087
70°	4203
75°	2753
80°	0
85°	0



TEST NUMBER: P573671

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-30 F4X-N-X-H-BL89BV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	363.4	11.3
10°-20°	881.5	27.5
20°-30°	1023.4	31.9
30°-40°	677.8	21.1
40°-50°	190.1	5.9
50°-60°	47.8	1.5
60°-70°	18.0	0.6
70°-80°	6.1	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2268.3	70.7
0°-40°	2946.1	91.8
0°-60°	3183.9	99.2
0°-90°	3208.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3208.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4028	
5°	3923	363
15°	3156	881
25°	2243	1023
35°	1087	678
45°	221	190
55°	52	48
65°	18	18
75°	6	6
85°	0	0
90°	0	



TEST NUMBER: P573671

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-30 F4X-N-X-H-BL89BV

CANDELA DISTRIBUTION (FULL):

	0°
0°	4027.8
2.5°	4010.3
5°	3923.1
7.5°	3771.9
10°	3585.9
12.5°	3376.6
15°	3155.9
17.5°	2940.8
20°	2702.7
22.5°	2481.7
25°	2243.3
27.5°	2016.8
30°	1726.2
32.5°	1418.1
35°	1086.9
37.5°	778.9
40°	528.8
42.5°	342.8
45°	220.9
47.5°	133.8
50°	87.2
52.5°	63.8
55°	52.2
57.5°	40.8
60°	29.1
62.5°	23.3
65°	17.5
67.5°	11.7
70°	11.7
72.5°	5.8
75°	5.8
77.5°	5.8
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)