

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573680

Luminaire Tested: **FLD4C-50-D010 FEU4C-X-90-30 F4X-W-X-H-BL85**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573680
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-50-D010 FEU4C-X-90-30 F4X-W-X-H-BL85
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 3000K, 90 CRI LEDS, 4LBWH TRIM
AND BOTTOM LENS, 0.187" CLEAR POLYCARBONATE

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3889.0 lumens
Efficiency: N/A
Efficacy: 66.6 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 58.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573680

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-30 F4X-W-X-H-BL85

Luminous Intensity Polar Plot





TEST NUMBER: P573680

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-30 F4X-W-X-H-BL85

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			50
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			102
1	112	109	106	104		110	107	104	102		103	101	99			99	97	96			96
2	105	100	95	91		103	98	93	90		95	91	88			91	88	86			89
3	99	91	85	80		97	90	84	80		87	82	78			84	80	77			82
4	92	83	77	72		90	82	76	71		80	75	70			78	73	70			76
5	87	77	70	65		85	76	69	64		74	68	64			72	67	63			70
6	81	71	64	58		80	70	63	58		68	62	58			67	61	57			65
7	76	65	58	53		75	65	58	53		63	57	53			62	56	52			61
8	72	60	53	49		70	60	53	49		59	53	48			58	52	48			57
9	68	56	49	45		66	56	49	45		55	49	44			54	48	44			53
10	64	52	46	41		63	52	46	41		51	45	41			50	45	41			49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	307957
5°	309133
10°	310075
15°	310083
20°	308385
25°	301160
30°	281477
35°	243757
40°	190412
45°	136613
50°	88759
55°	53119
60°	31082
65°	19971
70°	13290
75°	10016
80°	7499
85°	0



TEST NUMBER: P573680

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-30 F4X-W-X-H-BL85

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	238.7	6.1
10°-20°	687.8	17.7
20°-30°	1015.0	26.1
30°-40°	1001.6	25.8
40°-50°	612.9	15.8
50°-60°	235.0	6.0
60°-70°	73.5	1.9
70°-80°	21.5	0.6
80°-90°	2.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1941.5	49.9
0°-40°	2943.2	75.7
0°-60°	3791.1	97.5
0°-90°	3889.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3889.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2507	
5°	2507	239
15°	2438	688
25°	2222	1015
35°	1625	1002
45°	786	613
55°	248	235
65°	69	73
75°	21	22
85°	0	3
90°	0	



TEST NUMBER: P573680

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-30 F4X-W-X-H-BL85

CANDELA DISTRIBUTION (FULL):

	0°
0°	2506.7
2.5°	2512.0
5°	2506.7
7.5°	2501.4
10°	2485.6
12.5°	2464.4
15°	2438.0
17.5°	2406.3
20°	2358.8
22.5°	2306.2
25°	2221.7
27.5°	2116.0
30°	1984.2
32.5°	1820.7
35°	1625.3
37.5°	1408.9
40°	1187.3
42.5°	981.5
45°	786.3
47.5°	612.0
50°	464.4
52.5°	343.1
55°	248.0
57.5°	174.1
60°	126.5
62.5°	95.1
65°	68.7
67.5°	52.8
70°	37.0
72.5°	26.4
75°	21.1
77.5°	10.6
80°	10.6
82.5°	5.3
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)