

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573707

Luminaire Tested: **FLD4C-50-D010 FEU4C-X-90-35 F4X-N-X-H-BL89BV**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573707
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207666)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-50-D010 FEU4C-X-90-35 F4X-N-X-H-BL89BV
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 3500K, 90 CRI LEDS, 4LBNH TRIM
AND BOTTOM LENS, 0.125" CLEAR ACRYLIC

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3252.0 lumens
Efficiency: N/A
Efficacy: 55.7 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 58.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573707

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-35 F4X-N-X-H-BL89BV

Luminous Intensity Polar Plot





TEST NUMBER: P573707

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-35 F4X-N-X-H-BL89BV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	111	108	106		111	109	106	104		105	103	101		101	99	98		97	96	95
2	108	103	99	96		106	101	98	94		98	95	92		95	93	90		92	90	89
3	102	96	91	87		100	95	90	86		92	88	85		90	86	84		87	85	82
4	97	90	84	80		95	89	83	79		86	82	78		84	81	78		83	79	77
5	92	84	78	74		91	83	78	73		81	76	73		80	75	72		78	74	72
6	88	79	73	69		86	78	72	68		77	72	68		75	71	67		74	70	67
7	83	74	68	64		82	73	68	64		72	67	63		71	66	63		70	66	63
8	79	70	64	60		78	69	64	60		68	63	59		67	63	59		66	62	59
9	76	66	60	56		74	65	60	56		65	59	56		64	59	56		63	59	55
10	72	62	57	53		71	62	56	53		61	56	53		60	56	52		60	55	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	501611
5°	490442
10°	453474
15°	406898
20°	358183
25°	308263
30°	248239
35°	165259
40°	85960
45°	38918
50°	16896
55°	11331
60°	7248
65°	5145
70°	4239
75°	2801
80°	0
85°	0



TEST NUMBER: P573707

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-35 F4X-N-X-H-BL89BV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	368.4	11.3
10°-20°	893.6	27.5
20°-30°	1037.5	31.9
30°-40°	687.0	21.1
40°-50°	192.7	5.9
50°-60°	48.4	1.5
60°-70°	18.2	0.6
70°-80°	6.2	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2299.4	70.7
0°-40°	2986.5	91.8
0°-60°	3227.6	99.3
0°-90°	3252.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3252.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4083	
5°	3977	368
15°	3199	894
25°	2274	1037
35°	1102	687
45°	224	193
55°	53	48
65°	18	18
75°	6	6
85°	0	0
90°	0	



TEST NUMBER: P573707

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-35 F4X-N-X-H-BL89BV

CANDELA DISTRIBUTION (FULL):

	0°
0°	4083.0
2.5°	4065.3
5°	3976.9
7.5°	3823.6
10°	3635.1
12.5°	3422.9
15°	3199.2
17.5°	2981.2
20°	2739.7
22.5°	2515.8
25°	2274.1
27.5°	2044.5
30°	1749.9
32.5°	1437.5
35°	1101.9
37.5°	789.5
40°	536.0
42.5°	347.5
45°	224.0
47.5°	135.6
50°	88.4
52.5°	64.7
55°	52.9
57.5°	41.4
60°	29.5
62.5°	23.6
65°	17.7
67.5°	11.8
70°	11.8
72.5°	5.9
75°	5.9
77.5°	5.9
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)