

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573715

Luminaire Tested: **FLD4C-50-D010 FEU4C-X-90-35 F4X-W-X-H-BL84**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573715
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-50-D010 FEU4C-X-90-35 F4X-W-X-H-BL84
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 3500K, 90 CRI LEDS, 4LBWH TRIM
AND BOTTOM LENS, 0.125" CLEAR POLYCARBONATE

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4135.0 lumens
Efficiency: N/A
Efficacy: 70.8 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 58.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573715

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-35 F4X-W-X-H-BL84

Luminous Intensity Polar Plot





TEST NUMBER: P573715

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-35 F4X-W-X-H-BL84

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96
2	105	100	95	91	103	98	93	90	95	91	88		91	88	86		89
3	99	91	85	80	97	90	84	80	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	64	74	68	64		72	67	63		70
6	81	71	64	58	80	70	63	58	68	62	58		67	61	57		65
7	76	65	58	53	75	65	58	53	63	57	53		62	56	52		61
8	72	60	53	49	70	60	53	49	59	53	48		58	52	48		57
9	68	56	49	45	66	56	49	45	55	49	44		54	48	44		53
10	64	52	46	41	63	52	46	41	51	45	41		50	45	41		49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	327441
5°	328692
10°	329686
15°	329695
20°	327891
25°	320205
30°	299280
35°	259174
40°	202456
45°	145265
50°	94359
55°	56482
60°	33048
65°	21221
70°	14117
75°	10680
80°	7924
85°	0



TEST NUMBER: P573715

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-35 F4X-W-X-H-BL84

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	253.8	6.1
10°-20°	731.3	17.7
20°-30°	1079.2	26.1
30°-40°	1065.0	25.8
40°-50°	651.7	15.8
50°-60°	249.8	6.0
60°-70°	78.1	1.9
70°-80°	22.9	0.6
80°-90°	3.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2064.3	49.9
0°-40°	3129.3	75.7
0°-60°	4030.9	97.5
0°-90°	4135.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4135.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2665	
5°	2665	254
15°	2592	731
25°	2362	1079
35°	1728	1065
45°	836	652
55°	264	250
65°	73	78
75°	22	23
85°	0	3
90°	0	



TEST NUMBER: P573715

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-35 F4X-W-X-H-BL84

CANDELA DISTRIBUTION (FULL):

	0°
0°	2665.3
2.5°	2670.9
5°	2665.3
7.5°	2659.6
10°	2642.8
12.5°	2620.3
15°	2592.2
17.5°	2558.5
20°	2508.0
22.5°	2452.1
25°	2362.2
27.5°	2249.9
30°	2109.7
32.5°	1935.9
35°	1728.1
37.5°	1498.1
40°	1262.4
42.5°	1043.6
45°	836.1
47.5°	650.7
50°	493.7
52.5°	364.8
55°	263.7
57.5°	185.1
60°	134.5
62.5°	101.1
65°	73.0
67.5°	56.2
70°	39.3
72.5°	28.1
75°	22.5
77.5°	11.2
80°	11.2
82.5°	5.6
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)