

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573725

Luminaire Tested: **FLD4C-50-D010 FEU4C-X-90-35 F4X-W-X-LI-BL89BV**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573725
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-50-D010 FEU4C-X-90-35 F4X-W-X-LI-BL89BV
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 3500K, 90 CRI LEDS, 4LBWLI TRIM
AND BOTTOM LENS, 0.125" CLEAR ACRYLIC

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5154.0 lumens
Efficiency: N/A
Efficacy: 88.3 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 58.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573725

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-35 F4X-W-X-LI-BL89BV

Luminous Intensity Polar Plot



TEST NUMBER: P573725

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-35 F4X-W-X-LI-BL89BV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92						
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84						
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77						
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	72	70						
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64						
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	63	60	58						
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54						
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49						
9	69	59	52	48	68	58	52	47	57	51	47	56	51	47	55	50	47	45						
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42						

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	387947
5°	394534
10°	412369
15°	437677
20°	456851
25°	452885
30°	421179
35°	360303
40°	274528
45°	161023
50°	68805
55°	20262
60°	5799
65°	3430
70°	2119
75°	2801
80°	0
85°	0



TEST NUMBER: P573725

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-35 F4X-W-X-LI-BL89BV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	308.8	6.0
10°-20°	974.6	18.9
20°-30°	1520.4	29.5
30°-40°	1479.3	28.7
40°-50°	738.9	14.3
50°-60°	114.4	2.2
60°-70°	13.8	0.3
70°-80°	3.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2803.7	54.4
0°-40°	4283.0	83.1
0°-60°	5136.3	99.7
0°-90°	5154.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5154.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3158	
5°	3199	309
15°	3441	975
25°	3341	1520
35°	2402	1479
45°	927	739
55°	95	114
65°	12	14
75°	6	4
85°	0	0
90°	0	



TEST NUMBER: P573725

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-35 F4X-W-X-LI-BL89BV

CANDELA DISTRIBUTION (FULL):

	0°
0°	3157.8
2.5°	3169.6
5°	3199.2
7.5°	3246.5
10°	3305.6
12.5°	3382.1
15°	3441.2
17.5°	3488.5
20°	3494.4
22.5°	3453.1
25°	3341.0
27.5°	3175.6
30°	2969.0
32.5°	2709.5
35°	2402.4
37.5°	2065.8
40°	1711.8
42.5°	1334.1
45°	926.8
47.5°	596.1
50°	360.0
52.5°	194.8
55°	94.6
57.5°	41.4
60°	23.6
62.5°	17.7
65°	11.8
67.5°	11.8
70°	5.9
72.5°	5.9
75°	5.9
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)