

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573741

Luminaire Tested: **FLD4C-50-D010 FEU4C-X-90-40 F4X-N-X-H-BL86**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573741
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207666)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-50-D010 FEU4C-X-90-40 F4X-N-X-H-BL86
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 4000K, 90 CRI LEDS, 4LBNH TRIM
AND BOTTOM LENS, 0.250" CLEAR POLYCARBONATE

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2994.0 lumens
Efficiency: N/A
Efficacy: 51.3 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 58.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573741

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-40 F4X-N-X-H-BL86

Luminous Intensity Polar Plot





TEST NUMBER: P573741

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-40 F4X-N-X-H-BL86

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	111	108	106		111	109	106	104		105	103	101		101	99	98		97	96	95
2	108	103	99	96		106	101	98	94		98	95	92		95	93	90		92	90	89
3	102	96	91	87		100	95	90	86		92	88	85		90	86	84		87	85	82
4	97	90	84	80		95	89	83	79		86	82	78		84	81	78		83	79	77
5	92	84	78	74		91	83	78	73		81	76	73		80	75	72		78	74	72
6	88	79	73	69		86	78	72	68		77	72	68		75	71	67		74	70	67
7	83	74	68	64		82	73	68	64		72	67	63		71	66	63		70	66	63
8	79	70	64	60		78	69	64	60		68	63	59		67	63	59		66	62	59
9	76	66	60	56		74	65	60	56		65	59	56		64	59	56		63	59	55
10	72	62	57	53		71	62	56	53		61	56	53		60	56	52		60	55	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	461818
5°	451534
10°	417496
15°	374617
20°	329773
25°	283809
30°	228535
35°	152136
40°	79144
45°	35825
50°	15539
55°	10431
60°	6683
65°	4738
70°	3915
75°	2563
80°	0
85°	0



TEST NUMBER: P573741

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-40 F4X-N-X-H-BL86

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	339.2	11.3
10°-20°	822.7	27.5
20°-30°	955.2	31.9
30°-40°	632.5	21.1
40°-50°	177.4	5.9
50°-60°	44.6	1.5
60°-70°	16.8	0.6
70°-80°	5.7	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2117.0	70.7
0°-40°	2749.5	91.8
0°-60°	2971.5	99.2
0°-90°	2994.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2994.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3759	
5°	3661	339
15°	2945	823
25°	2094	955
35°	1014	633
45°	206	177
55°	49	45
65°	16	17
75°	5	6
85°	0	0
90°	0	



TEST NUMBER: P573741

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-40 F4X-N-X-H-BL86

CANDELA DISTRIBUTION (FULL):

	0°
0°	3759.1
2.5°	3742.8
5°	3661.4
7.5°	3520.3
10°	3346.7
12.5°	3151.4
15°	2945.4
17.5°	2744.7
20°	2522.4
22.5°	2316.2
25°	2093.7
27.5°	1882.3
30°	1611.0
32.5°	1323.5
35°	1014.4
37.5°	726.9
40°	493.5
42.5°	319.9
45°	206.2
47.5°	124.9
50°	81.3
52.5°	59.6
55°	48.7
57.5°	38.1
60°	27.2
62.5°	21.8
65°	16.3
67.5°	10.9
70°	10.9
72.5°	5.4
75°	5.4
77.5°	5.4
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)