

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573747

Luminaire Tested: **FLD4C-50-D010 FEU4C-X-90-40 F4X-N-X-LI-BL86**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573747
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208279)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-50-D010 FEU4C-X-90-40 F4X-N-X-LI-BL86
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 4000K, 90 CRI LEDS, 4LBNI TRIM
AND BOTTOM LENS, 0.250" CLEAR POLYCARBONATE

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3526.0 lumens
Efficiency: N/A
Efficacy: 60.4 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 58.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573747

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-40 F4X-N-X-LI-BL86

Luminous Intensity Polar Plot





TEST NUMBER: P573747

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-40 F4X-N-X-LI-BL86

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	110	108		112	110	108	106		106	104	103		102	101	100		99	98	97
2	109	105	102	99		107	103	100	98		100	98	95		97	95	93		95	93	92
3	105	99	95	92		103	98	94	91		95	92	89		93	90	88		91	89	87
4	101	94	89	86		99	93	88	85		91	87	84		89	86	83		87	84	82
5	96	89	84	80		95	88	84	80		87	82	79		85	81	79		83	80	78
6	92	85	80	76		91	84	79	76		83	78	75		81	78	75		80	77	74
7	89	81	76	72		88	80	75	72		79	75	71		78	74	71		77	73	71
8	85	77	72	68		84	77	72	68		76	71	68		75	71	68		74	70	67
9	82	74	69	65		81	73	68	65		72	68	65		72	68	65		71	67	64
10	79	71	66	62		78	70	65	62		69	65	62		69	65	62		68	64	62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1114760
5°	1003169
10°	777671
15°	562880
20°	389743
25°	284134
30°	206447
35°	122171
40°	51384
45°	16019
50°	2083
55°	1157
60°	1327
65°	1570
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P573747

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-40 F4X-N-X-LI-BL86

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	715.1	20.3
10°-20°	1224.2	34.7
20°-30°	972.9	27.6
30°-40°	515.1	14.6
40°-50°	88.7	2.5
50°-60°	6.6	0.2
60°-70°	3.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2912.2	82.6
0°-40°	3427.3	97.2
0°-60°	3522.7	99.9
0°-90°	3526.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3526.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9074	
5°	8134	715
15°	4426	1224
25°	2096	973
35°	815	515
45°	92	89
55°	5	7
65°	5	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P573747

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-40 F4X-N-X-LI-BL86

CANDELA DISTRIBUTION (FULL):

	0°
0°	9073.9
2.5°	8840.3
5°	8134.5
7.5°	7211.4
10°	6233.9
12.5°	5289.1
15°	4425.6
17.5°	3621.9
20°	2981.1
22.5°	2492.4
25°	2096.1
27.5°	1775.7
30°	1455.3
32.5°	1129.5
35°	814.6
37.5°	537.7
40°	320.4
42.5°	184.7
45°	92.2
47.5°	32.6
50°	10.9
52.5°	10.9
55°	5.4
57.5°	5.4
60°	5.4
62.5°	5.4
65°	5.4
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)