

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573757

Luminaire Tested: **FLD4C-50-D010 FEU4C-X-90-40 F4X-W-X-LI-BL84**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573757
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-50-D010 FEU4C-X-90-40 F4X-W-X-LI-BL84
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 4000K, 90 CRI LEDS, 4LBWLI TRIM
AND BOTTOM LENS, 0.125" CLEAR POLYCARBONATE

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4905.0 lumens
Efficiency: N/A
Efficacy: 84.0 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 58.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573757

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-40 F4X-W-X-LI-BL84

Luminous Intensity Polar Plot





TEST NUMBER: P573757

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-40 F4X-W-X-LI-BL84

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	107	105		110	108	105	103		104	102	100		100	98	97		96	95	94
2	106	101	97	93		104	99	95	92		96	93	90		93	90	88		90	88	86
3	100	93	87	83		98	92	86	82		89	85	81		86	83	80		84	81	78
4	94	86	79	75		92	84	79	74		82	77	73		80	76	72		78	75	72
5	88	79	72	68		87	78	72	67		76	71	67		74	70	66		73	69	65
6	83	73	66	62		82	72	66	61		71	65	61		69	64	60		68	63	60
7	78	68	61	56		77	67	61	56		66	60	56		64	59	55		63	59	55
8	74	63	56	52		72	62	56	51		61	55	51		60	55	51		59	54	51
9	69	59	52	48		68	58	52	47		57	51	47		56	51	47		55	50	47
10	66	55	48	44		65	54	48	44		53	48	44		53	47	44		52	47	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	369212
5°	375468
10°	392447
15°	416538
20°	434782
25°	431007
30°	400823
35°	342906
40°	261265
45°	153240
50°	65480
55°	19277
60°	5528
65°	3256
70°	2012
75°	2658
80°	0
85°	0



TEST NUMBER: P573757

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-40 F4X-W-X-LI-BL84

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	293.9	6.0
10°-20°	927.5	18.9
20°-30°	1446.9	29.5
30°-40°	1407.8	28.7
40°-50°	703.2	14.3
50°-60°	108.9	2.2
60°-70°	13.1	0.3
70°-80°	3.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2668.3	54.4
0°-40°	4076.1	83.1
0°-60°	4888.2	99.7
0°-90°	4905.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4905.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3005	
5°	3045	294
15°	3275	927
25°	3180	1447
35°	2286	1408
45°	882	703
55°	90	109
65°	11	13
75°	6	4
85°	0	0
90°	0	



TEST NUMBER: P573757

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-40 F4X-W-X-LI-BL84

CANDELA DISTRIBUTION (FULL):

	0°
0°	3005.3
2.5°	3016.5
5°	3044.6
7.5°	3089.6
10°	3145.9
12.5°	3218.7
15°	3275.0
17.5°	3320.0
20°	3325.6
22.5°	3286.2
25°	3179.6
27.5°	3022.1
30°	2825.5
32.5°	2578.6
35°	2286.4
37.5°	1966.0
40°	1629.1
42.5°	1269.6
45°	882.0
47.5°	567.3
50°	342.6
52.5°	185.4
55°	90.0
57.5°	39.4
60°	22.5
62.5°	16.9
65°	11.2
67.5°	11.2
70°	5.6
72.5°	5.6
75°	5.6
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)