

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573790

Luminaire Tested: **FLD4C-50-D010 FEU4C-X-90-50 F4X-W-X-H-BL89AM**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573790
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-50-D010 FEU4C-X-90-50 F4X-W-X-H-BL89AM
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 5000K, 90 CRI LEDS, 4LBWH TRIM
AND BOTTOM LENS, 0.125" OPAL POLYCARBONATE

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1833.0 lumens
Efficiency: N/A
Efficacy: 31.4 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 58.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573790

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-50 F4X-W-X-H-BL89AM

Luminous Intensity Polar Plot





TEST NUMBER: P573790

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-50 F4X-W-X-H-BL89AM

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96
2	105	100	95	91	103	98	93	90	95	91	88		91	88	86		89
3	99	91	85	80	97	90	84	80	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	64	74	68	64		72	67	63		70
6	81	71	64	58	80	70	63	58	68	62	58		67	61	57		65
7	76	65	58	53	75	65	58	53	63	57	53		62	56	52		61
8	72	60	53	49	70	60	53	49	59	53	48		58	52	48		57
9	68	56	49	45	66	56	49	45	55	49	44		54	48	44		53
10	64	52	46	41	63	52	46	41	51	45	41		50	45	41		49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	145151
5°	145706
10°	146143
15°	146151
20°	145354
25°	141938
30°	132667
35°	114882
40°	89745
45°	64388
50°	41837
55°	25039
60°	14644
65°	9419
70°	6250
75°	4747
80°	3537
85°	0



TEST NUMBER: P573790

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-50 F4X-W-X-H-BL89AM

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	112.5	6.1
10°-20°	324.2	17.7
20°-30°	478.4	26.1
30°-40°	472.1	25.8
40°-50°	288.9	15.8
50°-60°	110.7	6.0
60°-70°	34.6	1.9
70°-80°	10.2	0.6
80°-90°	1.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	915.1	49.9
0°-40°	1387.2	75.7
0°-60°	1786.9	97.5
0°-90°	1833.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1833.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1182	
5°	1182	113
15°	1149	324
25°	1047	478
35°	766	472
45°	371	289
55°	117	111
65°	32	35
75°	10	10
85°	0	1
90°	0	



TEST NUMBER: P573790

CATALOG NUMBER: FLD4C-50-D010 FEU4C-X-90-50 F4X-W-X-H-BL89AM

CANDELA DISTRIBUTION (FULL):

	0°
0°	1181.5
2.5°	1184.0
5°	1181.5
7.5°	1179.0
10°	1171.5
12.5°	1161.6
15°	1149.1
17.5°	1134.2
20°	1111.8
22.5°	1087.0
25°	1047.1
27.5°	997.4
30°	935.2
32.5°	858.2
35°	766.0
37.5°	664.1
40°	559.6
42.5°	462.6
45°	370.6
47.5°	288.5
50°	218.9
52.5°	161.7
55°	116.9
57.5°	82.0
60°	59.6
62.5°	44.8
65°	32.4
67.5°	24.9
70°	17.4
72.5°	12.4
75°	10.0
77.5°	5.0
80°	5.0
82.5°	2.5
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)