

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P974727

Luminaire Tested: FLR2-24-35HE-L835-CA125

Issue Date: 3/13/2025

Test Information

Test Method: LM-79-2019
Report Number: P974727
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-281-3)
Test Lab: INNOVATION CENTER
Issue Date: 3/13/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: FLR2-24-35HE-L835-CA125
Description: SHAPER SENSE CIRCLE

Light Source:
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3343.8 lumens
Efficiency: N/A
Efficacy: 130.6 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.27 / 1.39
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 25.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor:
Total Harmonic Distortion (THDi):
Frequency (hertz): 60
Stabilization Time: HR
Operation Time: HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P974727

CATALOG NUMBER: FLR2-24-35HE-L835-CA125

Luminous Intensity Polar Plot



TEST NUMBER: P974727

CATALOG NUMBER: FLR2-24-35HE-L835-CA125

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		100
1	109	105	100	97	106	102	99	95	98	95	92	94	92	89	91	89	87	85		85
2	99	91	85	79	97	89	83	78	86	81	76	83	78	75	80	76	73	71		71
3	91	80	72	66	88	79	71	65	76	69	64	73	68	63	70	66	62	60		60
4	83	71	62	56	81	70	62	55	67	60	55	65	59	54	63	57	53	51		51
5	76	64	55	48	74	62	54	48	60	53	47	58	52	47	56	51	46	44		44
6	70	57	48	42	69	56	48	42	54	47	41	53	46	41	51	45	41	38		38
7	65	52	43	37	64	51	43	37	49	42	37	48	41	36	47	41	36	34		34
8	61	47	39	33	59	47	38	33	45	38	33	44	37	32	43	37	32	30		30
9	57	43	35	30	55	43	35	30	42	34	29	41	34	29	39	33	29	27		27
10	53	40	32	27	52	39	32	27	38	31	27	38	31	26	37	31	26	25		25

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1592	1592	1592
5°	1595	1595	1594
10°	1596	1596	1595
15°	1597	1596	1596
20°	1595	1594	1592
25°	1592	1589	1586
30°	1585	1580	1577
35°	1574	1570	1565
40°	1561	1551	1549
45°	1540	1532	1527
50°	1512	1500	1495
55°	1476	1455	1453
60°	1414	1389	1389
65°	1323	1292	1296
70°	1191	1154	1151
75°	1000	960	955
80°	730	694	724
85°	412	380	386

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1540 cd/sqm

TEST NUMBER: P974727

CATALOG NUMBER: FLR2-24-35HE-L835-CA125

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	112.3	3.4
10°-20°	323.5	9.7
20°-30°	493.3	14.8
30°-40°	597.6	17.9
40°-50°	620.8	18.6
50°-60°	555.3	16.6
60°-70°	404.7	12.1
70°-80°	200.4	6.0
80°-90°	35.8	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	929.1	27.8
0°-40°	1526.7	45.7
0°-60°	2702.8	80.8
0°-90°	3343.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3343.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1183	1183	1183	1183	1183	
5°	1181	1181	1181	1181	1180	112
15°	1146	1146	1146	1147	1146	324
25°	1072	1071	1070	1070	1068	494
35°	958	957	956	954	953	600
45°	810	808	805	803	802	624
55°	629	624	620	620	619	561
65°	416	412	406	408	407	412
75°	192	189	185	188	184	205
85°	27	25	25	25	25	37
90°	0	0	0	0	0	

TEST NUMBER: P974727

CATALOG NUMBER: FLR2-24-35HE-L835-CA125

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1183.1	1183.1	1183.1	1183.1	1183.1
2.5°	1183.1	1182.7	1182.7	1183.1	1182.2
5°	1181.0	1181.4	1181.0	1181.0	1180.1
7.5°	1176.3	1175.9	1175.5	1175.9	1174.6
10°	1168.2	1168.2	1167.8	1168.2	1167.4
12.5°	1158.5	1158.5	1158.5	1158.9	1158.5
15°	1146.2	1145.7	1145.7	1146.6	1145.7
17.5°	1131.7	1131.3	1131.3	1130.9	1130.0
20°	1113.9	1113.9	1113.5	1113.1	1111.8
22.5°	1094.8	1094.4	1093.1	1093.1	1091.4
25°	1072.3	1071.0	1070.2	1069.8	1068.5
27.5°	1047.7	1046.0	1044.7	1043.9	1042.6
30°	1020.1	1018.4	1017.1	1015.8	1015.0
32.5°	990.4	989.5	987.4	987.0	985.3
35°	958.5	957.3	956.0	954.3	952.6
37.5°	924.6	923.3	920.3	919.5	918.2
40°	888.5	886.8	883.0	883.0	881.7
42.5°	849.9	848.2	845.6	843.9	843.1
45°	809.5	807.8	804.9	803.2	802.3
47.5°	766.7	765.4	762.0	760.7	759.4
50°	722.1	720.4	716.6	715.7	714.4
52.5°	675.4	674.5	669.4	669.0	667.7
55°	629.1	624.4	620.2	620.2	619.4
57.5°	578.2	574.8	569.3	569.3	568.4
60°	525.5	522.6	516.2	517.0	516.2
62.5°	474.2	467.8	461.9	464.4	462.3
65°	415.6	412.2	405.8	407.5	407.1
67.5°	362.1	355.7	349.8	353.2	351.5
70°	302.7	299.3	293.3	296.7	292.5
72.5°	246.6	243.7	237.7	241.5	237.3
75°	192.3	189.3	184.7	188.1	183.8
77.5°	140.9	138.8	134.6	138.0	138.8
80°	94.2	91.7	89.6	92.5	93.4
82.5°	55.2	53.5	52.6	53.1	55.2
85°	26.7	24.6	24.6	25.0	25.0
87.5°	7.2	6.4	7.2	7.6	8.1
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)