

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P696536

Luminaire Tested: **MRI-FEU4C-15-L930 F4X-W-X-LI**

Issue Date: 08/03/2023



Test Information

Test Method: LM-79-08
Report Number: P696536
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)
Test Lab: INNOVATION CENTER-P3
Issue Date: 08/03/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: MRI-FEU4C-15-L930 F4X-W-X-LI
Description: 4 INCH FAIL-SAFE MRI LED DOWNLIGHT WITH 3000K, 90 CRI LEDS, 4LBWLI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1529.1 lumens
Efficiency: N/A
Efficacy: 96.8 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P696536
CATALOG NUMBER: MRI-FEU4C-15-L930 F4X-W-X-LI

Luminous Intensity Polar Plot





TEST NUMBER: P696536

CATALOG NUMBER: MRI-FEU4C-15-L930 F4X-W-X-LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92		
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84		
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77		
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	72	70		
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64		
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	63	60	58		
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54		
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49		
9	69	59	52	48	68	58	52	47	57	51	47	56	51	47	55	50	47	45		
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	115089
5°	117046
10°	122329
15°	129845
20°	135536
25°	134361
30°	124949
35°	106888
40°	81438
45°	47761
50°	20412
55°	6019
60°	1720
65°	1017
70°	647
75°	854
80°	0
85°	0



TEST NUMBER: P696536
 CATALOG NUMBER: MRI-FEU4C-15-L930 F4X-W-X-LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.6	6.0
10°-20°	289.1	18.9
20°-30°	451.0	29.5
30°-40°	438.9	28.7
40°-50°	219.2	14.3
50°-60°	34.0	2.2
60°-70°	4.1	0.3
70°-80°	1.2	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	831.8	54.4
0°-40°	1270.6	83.1
0°-60°	1523.8	99.7
0°-90°	1529.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1529.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	937	
5°	949	92
15°	1021	289
25°	991	451
35°	713	439
45°	275	219
55°	28	34
65°	4	4
75°	2	1
85°	0	0
90°	0	

TEST NUMBER: P696536

CATALOG NUMBER: MRI-FEU4C-15-L930 F4X-W-X-LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	936.8
2.5°	940.3
5°	949.1
7.5°	963.1
10°	980.6
12.5°	1003.4
15°	1020.9
17.5°	1034.9
20°	1036.7
22.5°	1024.4
25°	991.2
27.5°	942.1
30°	880.8
32.5°	803.8
35°	712.7
37.5°	612.9
40°	507.8
42.5°	395.8
45°	274.9
47.5°	176.8
50°	106.8
52.5°	57.8
55°	28.1
57.5°	12.3
60°	7.0
62.5°	5.3
65°	3.5
67.5°	3.5
70°	1.8
72.5°	1.8
75°	1.8
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)