

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P696716

Luminaire Tested: **MRI-FEU4C-20-L930 F4X-W-X-LI**

Issue Date: 08/03/2023



Test Information

Test Method: LM-79-08
Report Number: P696716
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)
Test Lab: INNOVATION CENTER-P3
Issue Date: 08/03/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: MRI-FEU4C-20-L930 F4X-W-X-LI
Description: 4 INCH FAIL-SAFE MRI LED DOWNLIGHT WITH 3000K, 90 CRI LEDS, 4LBWLI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1973.0 lumens
Efficiency: N/A
Efficacy: 90.5 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 21.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P696716
CATALOG NUMBER: MRI-FEU4C-20-L930 F4X-W-X-LI

Luminous Intensity Polar Plot





TEST NUMBER: P696716

CATALOG NUMBER: MRI-FEU4C-20-L930 F4X-W-X-LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92		
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84		
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77		
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	72	70		
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64		
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	63	60	58		
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54		
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49		
9	69	59	52	48	68	58	52	47	57	51	47	56	51	47	55	50	47	45		
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	148505
5°	151033
10°	157857
15°	167544
20°	174888
25°	173373
30°	161237
35°	137933
40°	105093
45°	61643
50°	26337
55°	7754
60°	2211
65°	1308
70°	826
75°	1092
80°	0
85°	0

TEST NUMBER: P696716
 CATALOG NUMBER: MRI-FEU4C-20-L930 F4X-W-X-LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	118.2	6.0
10°-20°	373.1	18.9
20°-30°	582.0	29.5
30°-40°	566.3	28.7
40°-50°	282.9	14.3
50°-60°	43.8	2.2
60°-70°	5.3	0.3
70°-80°	1.5	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1073.3	54.4
0°-40°	1639.6	83.1
0°-60°	1966.2	99.7
0°-90°	1973.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1973.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1209	
5°	1225	118
15°	1317	373
25°	1279	582
35°	920	566
45°	355	283
55°	36	44
65°	4	5
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P696716
CATALOG NUMBER: MRI-FEU4C-20-L930 F4X-W-X-LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1208.8
2.5°	1213.4
5°	1224.7
7.5°	1242.8
10°	1265.4
12.5°	1294.7
15°	1317.3
17.5°	1335.4
20°	1337.7
22.5°	1321.9
25°	1279.0
27.5°	1215.6
30°	1136.6
32.5°	1037.2
35°	919.7
37.5°	790.8
40°	655.3
42.5°	510.7
45°	354.8
47.5°	228.2
50°	137.8
52.5°	74.6
55°	36.2
57.5°	15.8
60°	9.0
62.5°	6.8
65°	4.5
67.5°	4.5
70°	2.3
72.5°	2.3
75°	2.3
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)