

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P696836

Luminaire Tested: **MRI-FEU4C-25-L927 F4X-M-X-LI**

Issue Date: 08/03/2023



Test Information

Test Method: LM-79-08
Report Number: P696836
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205108)
Test Lab: INNOVATION CENTER-P3
Issue Date: 08/03/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: MRI-FEU4C-25-L927 F4X-M-X-LI
Description: 4 INCH FAIL-SAFE MRI LED DOWNLIGHT WITH 2700K, 90 CRI LEDS, 4LBMLI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2651.0 lumens
Efficiency: N/A
Efficacy: 83.9 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P696836
CATALOG NUMBER: MRI-FEU4C-25-L927 F4X-M-X-LI

Luminous Intensity Polar Plot





TEST NUMBER: P696836

CATALOG NUMBER: MRI-FEU4C-25-L927 F4X-M-X-LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50			
RCR																						
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102	100
1	114	111	109	106		111	109	107	105		105	103	101		101	100	98		98	97	96	94
2	108	103	100	96		106	102	98	95		99	96	93		96	93	91		93	91	89	88
3	103	97	92	88		101	95	91	87		93	89	86		90	87	85		88	85	83	82
4	98	91	85	81		96	89	84	81		87	83	80		85	82	79		83	80	78	76
5	93	85	79	75		91	84	79	75		82	78	74		81	77	73		79	76	73	71
6	89	80	74	70		87	79	74	70		78	73	69		76	72	69		75	71	68	67
7	84	75	69	65		83	75	69	65		73	68	65		72	68	64		71	67	64	63
8	80	71	65	61		79	70	65	61		69	64	61		68	64	60		67	63	60	59
9	77	67	61	57		75	67	61	57		66	61	57		65	60	57		64	60	57	55
10	73	64	58	54		72	63	58	54		62	57	54		62	57	54		61	57	54	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	407579
5°	403697
10°	382542
15°	347310
20°	306907
25°	265333
30°	207398
35°	127195
40°	65288
45°	25940
50°	8429
55°	2892
60°	2482
65°	1977
70°	1221
75°	1614
80°	0
85°	0



TEST NUMBER: P696836
 CATALOG NUMBER: MRI-FEU4C-25-L927 F4X-M-X-LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	305.6	11.5
10°-20°	760.9	28.7
20°-30°	884.5	33.4
30°-40°	541.6	20.4
40°-50°	134.5	5.1
50°-60°	15.7	0.6
60°-70°	5.9	0.2
70°-80°	2.2	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1951.0	73.6
0°-40°	2492.7	94.0
0°-60°	2642.9	99.7
0°-90°	2651.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2651.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3318	
5°	3274	306
15°	2731	761
25°	1957	885
35°	848	542
45°	149	135
55°	14	16
65°	7	6
75°	3	2
85°	0	0
90°	0	



TEST NUMBER: P696836
CATALOG NUMBER: MRI-FEU4C-25-L927 F4X-M-X-LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	3317.6
2.5°	3314.2
5°	3273.5
7.5°	3185.3
10°	3066.5
12.5°	2910.5
15°	2730.7
17.5°	2537.4
20°	2347.5
22.5°	2157.4
25°	1957.4
27.5°	1726.7
30°	1462.0
32.5°	1153.3
35°	848.1
37.5°	597.0
40°	407.1
42.5°	254.4
45°	149.3
47.5°	84.8
50°	44.1
52.5°	20.4
55°	13.5
57.5°	10.1
60°	10.1
62.5°	6.8
65°	6.8
67.5°	3.4
70°	3.4
72.5°	3.4
75°	3.4
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)