

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P696842

Luminaire Tested: **MRI-FEU4C-25-L927 F4X-N-X-H**

Issue Date: 08/03/2023



Test Information

Test Method: LM-79-08
Report Number: P696842
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207666)
Test Lab: INNOVATION CENTER-P3
Issue Date: 08/03/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: MRI-FEU4C-25-L927 F4X-N-X-H
Description: 4 INCH FAIL-SAFE MRI LED DOWNLIGHT WITH 2700K, 90 CRI LEDS, 4LBNH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1765.9 lumens
Efficiency: N/A
Efficacy: 55.9 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P696842
CATALOG NUMBER: MRI-FEU4C-25-L927 F4X-N-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P696842

CATALOG NUMBER: MRI-FEU4C-25-L927 F4X-N-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50			
RCR																				0		
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102	100
1	113	111	108	106		111	109	106	104		105	103	101		101	99	98		97	96	95	93
2	108	103	99	96		106	101	98	94		98	95	92		95	93	90		92	90	89	87
3	102	96	91	87		100	95	90	86		92	88	85		90	86	84		87	85	82	81
4	97	90	84	80		95	89	83	79		86	82	78		84	81	78		83	79	77	75
5	92	84	78	74		91	83	78	73		81	76	73		80	75	72		78	74	72	70
6	88	79	73	69		86	78	72	68		77	72	68		75	71	67		74	70	67	65
7	83	74	68	64		82	73	68	64		72	67	63		71	66	63		70	66	63	61
8	79	70	64	60		78	69	64	60		68	63	59		67	63	59		66	62	59	58
9	76	66	60	56		74	65	60	56		65	59	56		64	59	56		63	59	55	54
10	72	62	57	53		71	62	56	53		61	56	53		60	56	52		60	55	52	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	272403
5°	266340
10°	246254
15°	220962
20°	194512
25°	167395
30°	134809
35°	89746
40°	46685
45°	21127
50°	9174
55°	6147
60°	3931
65°	2791
70°	2299
75°	1519
80°	0
85°	0



TEST NUMBER: P696842
 CATALOG NUMBER: MRI-FEU4C-25-L927 F4X-N-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	200.0	11.3
10°-20°	485.3	27.5
20°-30°	563.4	31.9
30°-40°	373.1	21.1
40°-50°	104.6	5.9
50°-60°	26.3	1.5
60°-70°	9.9	0.6
70°-80°	3.4	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1248.7	70.7
0°-40°	1621.8	91.8
0°-60°	1752.7	99.3
0°-90°	1765.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1765.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2217	
5°	2160	200
15°	1737	485
25°	1235	563
35°	598	373
45°	122	105
55°	29	26
65°	10	10
75°	3	3
85°	0	0
90°	0	

TEST NUMBER: P696842

CATALOG NUMBER: MRI-FEU4C-25-L927 F4X-N-X-H

CANDELA DISTRIBUTION (FULL):

0°	
0°	2217.3
2.5°	2207.7
5°	2159.7
7.5°	2076.4
10°	1974.0
12.5°	1858.8
15°	1737.3
17.5°	1618.9
20°	1487.8
22.5°	1366.2
25°	1234.9
27.5°	1110.2
30°	950.3
32.5°	780.7
35°	598.4
37.5°	428.8
40°	291.1
42.5°	188.7
45°	121.6
47.5°	73.6
50°	48.0
52.5°	35.1
55°	28.7
57.5°	22.5
60°	16.0
62.5°	12.8
65°	9.6
67.5°	6.4
70°	6.4
72.5°	3.2
75°	3.2
77.5°	3.2
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)