

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P696878

Luminaire Tested: **MRI-FEU4C-25-L930 F4X-N-X-H**

Issue Date: 08/03/2023



Test Information

Test Method: LM-79-08
Report Number: P696878
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207666)
Test Lab: INNOVATION CENTER-P3
Issue Date: 08/03/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: MRI-FEU4C-25-L930 F4X-N-X-H
Description: 4 INCH FAIL-SAFE MRI LED DOWNLIGHT WITH 3000K, 90 CRI LEDS, 4LBNH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1836.0 lumens
Efficiency: N/A
Efficacy: 58.1 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P696878

CATALOG NUMBER: MRI-FEU4C-25-L930 F4X-N-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P696878

CATALOG NUMBER: MRI-FEU4C-25-L930 F4X-N-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93		
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87		
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81		
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75		
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70		
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65		
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61		
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58		
9	76	66	60	56	74	65	60	56	65	59	56	64	59	56	63	59	55	54		
10	72	62	57	53	71	62	56	53	61	56	53	60	56	52	60	55	52	51		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	283202
5°	276897
10°	256022
15°	229726
20°	202225
25°	174038
30°	140142
35°	93300
40°	48529
45°	21961
50°	9537
55°	6404
60°	4103
65°	2907
70°	2407
75°	1566
80°	0
85°	0



TEST NUMBER: P696878

CATALOG NUMBER: MRI-FEU4C-25-L930 F4X-N-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	208.0	11.3
10°-20°	504.5	27.5
20°-30°	585.7	31.9
30°-40°	387.9	21.1
40°-50°	108.8	5.9
50°-60°	27.3	1.5
60°-70°	10.3	0.6
70°-80°	3.5	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1298.2	70.7
0°-40°	1686.1	91.8
0°-60°	1822.2	99.3
0°-90°	1836.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1836.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2305	
5°	2245	208
15°	1806	504
25°	1284	586
35°	622	388
45°	126	109
55°	30	27
65°	10	10
75°	3	3
85°	0	0
90°	0	



TEST NUMBER: P696878

CATALOG NUMBER: MRI-FEU4C-25-L930 F4X-N-X-H

CANDELA DISTRIBUTION (FULL):

0°	
0°	2305.2
2.5°	2295.2
5°	2245.3
7.5°	2158.7
10°	2052.3
12.5°	1932.5
15°	1806.2
17.5°	1683.1
20°	1546.8
22.5°	1420.3
25°	1283.9
27.5°	1154.3
30°	987.9
32.5°	811.6
35°	622.1
37.5°	445.8
40°	302.6
42.5°	196.2
45°	126.4
47.5°	76.6
50°	49.9
52.5°	36.5
55°	29.9
57.5°	23.3
60°	16.7
62.5°	13.3
65°	10.0
67.5°	6.7
70°	6.7
72.5°	3.3
75°	3.3
77.5°	3.3
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)