

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P696944

Luminaire Tested: **MRI-FEU4C-25-L940 F4X-M-X-LI**

Issue Date: 08/03/2023



Test Information

Test Method: LM-79-08
Report Number: P696944
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205108)
Test Lab: INNOVATION CENTER-P3
Issue Date: 08/03/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: MRI-FEU4C-25-L940 F4X-M-X-LI
Description: 4 INCH FAIL-SAFE MRI LED DOWNLIGHT WITH 4000K, 90 CRI LEDS, 4LBMLI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2799.0 lumens
Efficiency: N/A
Efficacy: 88.6 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P696944
CATALOG NUMBER: MRI-FEU4C-25-L940 F4X-M-X-LI

Luminous Intensity Polar Plot





TEST NUMBER: P696944

CATALOG NUMBER: MRI-FEU4C-25-L940 F4X-M-X-LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	106	111	109	107	105	105	103	101		101	100	98		98
2	108	103	100	96	106	102	98	95	99	96	93		96	93	91		93
3	103	97	92	88	101	95	91	87	93	89	86		90	87	85		88
4	98	91	85	81	96	89	84	81	87	83	80		85	82	79		83
5	93	85	79	75	91	84	79	75	82	78	74		81	77	73		79
6	89	80	74	70	87	79	74	70	78	73	69		76	72	69		75
7	84	75	69	65	83	75	69	65	73	68	65		72	68	64		71
8	80	71	65	61	79	70	65	61	69	64	61		68	64	60		67
9	77	67	61	57	75	67	61	57	66	61	57		65	60	57		64
10	73	64	58	54	72	63	58	54	62	57	54		62	57	54		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	430331
5°	426240
10°	403899
15°	366706
20°	324034
25°	280136
30°	218988
35°	134289
40°	68929
45°	27382
50°	8887
55°	3063
60°	2629
65°	2093
70°	1293
75°	1709
80°	0
85°	0



TEST NUMBER: P696944
 CATALOG NUMBER: MRI-FEU4C-25-L940 F4X-M-X-LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	322.7	11.5
10°-20°	803.4	28.7
20°-30°	933.9	33.4
30°-40°	571.9	20.4
40°-50°	142.0	5.1
50°-60°	16.6	0.6
60°-70°	6.2	0.2
70°-80°	2.4	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2059.9	73.6
0°-40°	2631.8	94.0
0°-60°	2790.4	99.7
0°-90°	2799.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2799.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3503	
5°	3456	323
15°	2883	803
25°	2067	934
35°	895	572
45°	158	142
55°	14	17
65°	7	6
75°	4	2
85°	0	0
90°	0	



TEST NUMBER: P696944
CATALOG NUMBER: MRI-FEU4C-25-L940 F4X-M-X-LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	3502.8
2.5°	3499.2
5°	3456.3
7.5°	3363.1
10°	3237.7
12.5°	3073.0
15°	2883.2
17.5°	2679.0
20°	2478.5
22.5°	2277.9
25°	2066.6
27.5°	1823.1
30°	1543.7
32.5°	1217.7
35°	895.4
37.5°	630.3
40°	429.8
42.5°	268.6
45°	157.6
47.5°	89.6
50°	46.5
52.5°	21.5
55°	14.3
57.5°	10.7
60°	10.7
62.5°	7.2
65°	7.2
67.5°	3.6
70°	3.6
72.5°	3.6
75°	3.6
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)