

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P697204

Luminaire Tested: **MRI-FEU6C-10-L927 F6X-M-X-LI**

Issue Date: 08/03/2023



Test Information

Test Method: LM-79-08
Report Number: P697204
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205108)
Test Lab: INNOVATION CENTER-P3
Issue Date: 08/03/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: MRI-FEU6C-10-L927 F6X-M-X-LI
Description: 6 INCH FAIL-SAFE MRI LED DOWNLIGHT WITH 2700K, 90 CRI LEDS, 6LBMLI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 885.9 lumens
Efficiency: N/A
Efficacy: 90.9 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 9.75
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P697204
CATALOG NUMBER: MRI-FEU6C-10-L927 F6X-M-X-LI

Luminous Intensity Polar Plot





TEST NUMBER: P697204

CATALOG NUMBER: MRI-FEU6C-10-L927 F6X-M-X-LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	106	111	109	107	105	105	103	101		101	100	98		98
2	108	103	100	96	106	102	98	95	99	96	93		96	93	91		93
3	103	97	92	88	101	95	91	87	93	89	86		90	87	85		88
4	98	91	85	81	96	89	84	81	87	83	80		85	82	79		83
5	93	85	79	75	91	84	79	75	82	78	74		81	77	73		79
6	89	80	74	70	87	79	74	70	78	73	69		76	72	69		75
7	84	75	69	65	83	75	69	65	73	68	65		72	68	64		71
8	80	71	65	61	79	70	65	61	69	64	61		68	64	60		67
9	77	67	61	57	75	67	61	57	66	61	57		65	60	57		64
10	73	64	58	54	72	63	58	54	62	57	54		62	57	54		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	60785
5°	60208
10°	57052
15°	51794
20°	45772
25°	39571
30°	30929
35°	18966
40°	9733
45°	3869
50°	1254
55°	430
60°	373
65°	298
70°	176
75°	233
80°	0
85°	0



TEST NUMBER: P697204
 CATALOG NUMBER: MRI-FEU6C-10-L927 F6X-M-X-LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.1	11.5
10°-20°	254.3	28.7
20°-30°	295.6	33.4
30°-40°	181.0	20.4
40°-50°	45.0	5.1
50°-60°	5.2	0.6
60°-70°	2.0	0.2
70°-80°	0.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	652.1	73.6
0°-40°	833.1	94.0
0°-60°	883.3	99.7
0°-90°	885.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	885.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1109	
5°	1094	102
15°	913	254
25°	654	296
35°	283	181
45°	50	45
55°	4	5
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P697204

CATALOG NUMBER: MRI-FEU6C-10-L927 F6X-M-X-LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1108.8
2.5°	1107.6
5°	1094.1
7.5°	1064.6
10°	1024.9
12.5°	972.7
15°	912.6
17.5°	848.0
20°	784.6
22.5°	721.0
25°	654.2
27.5°	577.1
30°	488.6
32.5°	385.5
35°	283.4
37.5°	199.5
40°	136.0
42.5°	85.0
45°	49.9
47.5°	28.4
50°	14.7
52.5°	6.8
55°	4.5
57.5°	3.4
60°	3.4
62.5°	2.3
65°	2.3
67.5°	1.1
70°	1.1
72.5°	1.1
75°	1.1
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)