

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P698034

Luminaire Tested: **MRI-FEU6C-20-L950 F6X-M-X-H**

Issue Date: 08/03/2023



Test Information

Test Method: LM-79-08
Report Number: P698034
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203254)
Test Lab: INNOVATION CENTER-P3
Issue Date: 08/03/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: MRI-FEU6C-20-L950 F6X-M-X-H
Description: 6 INCH FAIL-SAFE MRI LED DOWNLIGHT WITH 5000K, 90 CRI LEDS, 6LBMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1543.0 lumens
Efficiency: N/A
Efficacy: 70.8 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 21.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P698034
CATALOG NUMBER: MRI-FEU6C-20-L950 F6X-M-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P698034
 CATALOG NUMBER: MRI-FEU6C-20-L950 F6X-M-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			20	
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92	92	92	92
2	107	102	97	93	105	100	96	92	97	93	90	94	91	88	91	89	87	85	85	85	85
3	101	94	88	84	99	92	88	84	90	86	82	87	84	81	85	82	80	78	78	78	78
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72	72	72	72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66	66	66	66
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61	61	61	61
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57	57	57	57
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53	53	53	53
9	72	62	56	51	71	61	55	51	60	55	51	60	55	51	59	54	51	49	49	49	49
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	46	46	46	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	83710
5°	82214
10°	78016
15°	73156
20°	68128
25°	62774
30°	52306
35°	36868
40°	23494
45°	14009
50°	8273
55°	5266
60°	3618
65°	2568
70°	1763
75°	1398
80°	695
85°	0



TEST NUMBER: P698034
 CATALOG NUMBER: MRI-FEU6C-20-L950 F6X-M-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	139.6	9.0
10°-20°	361.2	23.4
20°-30°	468.0	30.3
30°-40°	347.5	22.5
40°-50°	146.7	9.5
50°-60°	52.1	3.4
60°-70°	20.1	1.3
70°-80°	6.9	0.5
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	968.8	62.8
0°-40°	1316.3	85.3
0°-60°	1515.1	98.2
0°-90°	1543.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1543.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1527	
5°	1494	140
15°	1289	361
25°	1038	468
35°	551	347
45°	181	147
55°	55	52
65°	20	20
75°	7	7
85°	0	1
90°	0	



TEST NUMBER: P698034
CATALOG NUMBER: MRI-FEU6C-20-L950 F6X-M-X-H

CANDELA DISTRIBUTION (FULL):

0°	
0°	1527.0
2.5°	1522.6
5°	1494.0
7.5°	1452.1
10°	1401.5
12.5°	1346.3
15°	1289.0
17.5°	1225.2
20°	1167.8
22.5°	1108.4
25°	1037.8
27.5°	940.9
30°	826.3
32.5°	691.9
35°	550.9
37.5°	431.9
40°	328.3
42.5°	244.6
45°	180.7
47.5°	132.2
50°	97.0
52.5°	72.7
55°	55.1
57.5°	41.8
60°	33.0
62.5°	24.3
65°	19.8
67.5°	15.4
70°	11.0
72.5°	8.8
75°	6.6
77.5°	4.4
80°	2.2
82.5°	2.2
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)