

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P698094

Luminaire Tested: **MRI-FEU6C-25-L927 F6X-M-X-H**

Issue Date: 08/03/2023



Test Information

Test Method: LM-79-08
Report Number: P698094
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203254)
Test Lab: INNOVATION CENTER-P3
Issue Date: 08/03/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: MRI-FEU6C-25-L927 F6X-M-X-H
Description: 6 INCH FAIL-SAFE MRI LED DOWNLIGHT WITH 2700K, 90 CRI LEDS, 6LBMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1798.0 lumens
Efficiency: N/A
Efficacy: 57.1 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 31.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P698094
CATALOG NUMBER: MRI-FEU6C-25-L927 F6X-M-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P698094

CATALOG NUMBER: MRI-FEU6C-25-L927 F6X-M-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	113	110	107	105	111	108	105	103	104	102	100		100	99	97		92
2	107	102	97	93	105	100	96	92	97	93	90		94	91	88		85
3	101	94	88	84	99	92	88	84	90	86	82		87	84	81		78
4	95	87	81	76	93	86	80	76	84	79	75		82	78	74		72
5	90	81	75	70	88	80	74	70	78	73	69		76	72	68		66
6	85	75	69	64	83	75	69	64	73	68	64		72	67	63		61
7	80	70	64	59	79	70	64	59	68	63	59		67	62	59		57
8	76	66	60	55	75	65	59	55	64	59	55		63	58	55		53
9	72	62	56	51	71	61	55	51	60	55	51		60	55	51		49
10	69	58	52	48	68	58	52	48	57	52	48		56	51	48		46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	97547
5°	95801
10°	90908
15°	85245
20°	79387
25°	73147
30°	60952
35°	42958
40°	27380
45°	16327
50°	9637
55°	6136
60°	4221
65°	2996
70°	2068
75°	1631
80°	789
85°	0



TEST NUMBER: P698094
 CATALOG NUMBER: MRI-FEU6C-25-L927 F6X-M-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.7	9.0
10°-20°	420.9	23.4
20°-30°	545.3	30.3
30°-40°	404.9	22.5
40°-50°	170.9	9.5
50°-60°	60.7	3.4
60°-70°	23.4	1.3
70°-80°	8.1	0.5
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1128.9	62.8
0°-40°	1533.8	85.3
0°-60°	1765.4	98.2
0°-90°	1798.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1798.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1779	
5°	1741	163
15°	1502	421
25°	1209	545
35°	642	405
45°	211	171
55°	64	61
65°	23	23
75°	8	8
85°	0	1
90°	0	



TEST NUMBER: P698094
CATALOG NUMBER: MRI-FEU6C-25-L927 F6X-M-X-H

CANDELA DISTRIBUTION (FULL):

0°	
0°	1779.4
2.5°	1774.2
5°	1740.9
7.5°	1692.0
10°	1633.1
12.5°	1568.8
15°	1502.0
17.5°	1427.6
20°	1360.8
22.5°	1291.5
25°	1209.3
27.5°	1096.3
30°	962.9
32.5°	806.2
35°	641.9
37.5°	503.3
40°	382.6
42.5°	285.0
45°	210.6
47.5°	154.0
50°	113.0
52.5°	84.7
55°	64.2
57.5°	48.7
60°	38.5
62.5°	28.3
65°	23.1
67.5°	17.9
70°	12.9
72.5°	10.2
75°	7.7
77.5°	5.2
80°	2.5
82.5°	2.5
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)