

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P698194

Luminaire Tested: **MRI-FEU6C-25-L930 F6X-W-X-H**

Issue Date: 08/03/2023



Test Information

Test Method: LM-79-08
Report Number: P698194
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P202739)
Test Lab: INNOVATION CENTER-P3
Issue Date: 08/03/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: MRI-FEU6C-25-L930 F6X-W-X-H
Description: 6 INCH FAIL-SAFE MRI LED DOWNLIGHT WITH 3000K, 90 CRI LEDS, 6LBWH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2263.1 lumens
Efficiency: N/A
Efficacy: 71.8 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 31.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P698194
CATALOG NUMBER: MRI-FEU6C-25-L930 F6X-W-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P698194

CATALOG NUMBER: MRI-FEU6C-25-L930 F6X-W-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	112	109	106	103	110	107	104	101	103	100	98		99	97	95		91
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		81
3	98	90	84	79	96	89	83	78	86	81	77		83	79	76		73
4	92	82	75	70	90	81	75	70	79	73	69		77	72	68		65
5	86	75	68	63	84	74	68	63	72	66	62		71	65	61		59
6	80	69	62	57	78	68	61	56	67	61	56		65	60	56		53
7	75	64	56	51	73	63	56	51	62	55	51		60	55	51		49
8	70	59	52	47	69	58	51	47	57	51	46		56	50	46		44
9	66	55	48	43	65	54	47	43	53	47	43		52	47	42		41
10	62	51	44	40	61	50	44	39	50	43	39		49	43	39		38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	76513
5°	76486
10°	75900
15°	75392
20°	74241
25°	72549
30°	68308
35°	61817
40°	51618
45°	39554
50°	28016
55°	17662
60°	9966
65°	6473
70°	4231
75°	3114
80°	1863
85°	1887



TEST NUMBER: P698194
 CATALOG NUMBER: MRI-FEU6C-25-L930 F6X-W-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.8	5.8
10°-20°	374.1	16.5
20°-30°	548.5	24.2
30°-40°	570.8	25.2
40°-50°	394.9	17.5
50°-60°	172.0	7.6
60°-70°	52.8	2.3
70°-80°	15.8	0.7
80°-90°	2.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1054.4	46.6
0°-40°	1625.2	71.8
0°-60°	2192.1	96.9
0°-90°	2263.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2263.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1396	
5°	1390	132
15°	1328	374
25°	1199	548
35°	924	571
45°	510	395
55°	185	172
65°	50	53
75°	15	16
85°	3	2
90°	0	

TEST NUMBER: P698194

CATALOG NUMBER: MRI-FEU6C-25-L930 F6X-W-X-H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1395.7
2.5°	1398.7
5°	1389.9
7.5°	1378.2
10°	1363.5
12.5°	1348.8
15°	1328.4
17.5°	1301.9
20°	1272.6
22.5°	1240.4
25°	1199.4
27.5°	1146.5
30°	1079.1
32.5°	1008.7
35°	923.7
37.5°	829.9
40°	721.3
42.5°	612.9
45°	510.2
47.5°	413.4
50°	328.5
52.5°	249.3
55°	184.8
57.5°	132.0
60°	90.9
62.5°	67.5
65°	49.9
67.5°	38.2
70°	26.4
72.5°	20.6
75°	14.7
77.5°	8.7
80°	5.9
82.5°	3.0
85°	3.0
87.5°	0.0
90°	0.0

(END OF REPORT)