

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P698534

Luminaire Tested: **MRI-FEU6C-30-L935 F6X-N-X-H**

Issue Date: 08/03/2023



Test Information

Test Method: LM-79-08
Report Number: P698534
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203666)
Test Lab: INNOVATION CENTER-P3
Issue Date: 08/03/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: MRI-FEU6C-30-L935 F6X-N-X-H
Description: 6 INCH FAIL-SAFE MRI LED DOWNLIGHT WITH 3500K, 90 CRI LEDS, 6LBNH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1915.0 lumens
Efficiency: N/A
Efficacy: 60.6 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 31.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P698534

CATALOG NUMBER: MRI-FEU6C-30-L935 F6X-N-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P698534

CATALOG NUMBER: MRI-FEU6C-30-L935 F6X-N-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93		
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87		
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81		
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75		
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70		
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65		
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61		
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58		
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54		
10	72	62	57	53	71	62	57	53	61	56	53	60	56	52	60	55	52	51		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	134573
5°	131246
10°	121101
15°	107214
20°	93096
25°	79626
30°	65649
35°	43232
40°	23236
45°	10288
50°	4170
55°	3011
60°	1908
65°	1362
70°	1122
75°	741
80°	1105
85°	0



TEST NUMBER: P698534
 CATALOG NUMBER: MRI-FEU6C-30-L935 F6X-N-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	220.8	11.5
10°-20°	526.4	27.5
20°-30°	603.1	31.5
30°-40°	405.2	21.2
40°-50°	115.8	6.0
50°-60°	28.4	1.5
60°-70°	10.7	0.6
70°-80°	4.2	0.2
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1350.3	70.5
0°-40°	1755.5	91.7
0°-60°	1899.6	99.2
0°-90°	1915.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1915.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2455	
5°	2385	221
15°	1889	526
25°	1316	603
35°	646	405
45°	133	116
55°	32	28
65°	10	11
75°	4	4
85°	0	0
90°	0	

TEST NUMBER: P698534

CATALOG NUMBER: MRI-FEU6C-30-L935 F6X-N-X-H

CANDELA DISTRIBUTION (FULL):

0°	
0°	2454.8
2.5°	2437.4
5°	2385.0
7.5°	2290.6
10°	2175.5
12.5°	2028.7
15°	1889.1
17.5°	1742.5
20°	1595.8
22.5°	1456.1
25°	1316.4
27.5°	1187.2
30°	1037.1
32.5°	838.0
35°	646.0
37.5°	471.4
40°	324.7
42.5°	213.0
45°	132.7
47.5°	80.3
50°	48.9
52.5°	38.4
55°	31.5
57.5°	24.5
60°	17.4
62.5°	13.9
65°	10.5
67.5°	7.0
70°	7.0
72.5°	3.5
75°	3.5
77.5°	3.5
80°	3.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)