

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P698604

Luminaire Tested: **MRI-FEU6C-30-L940 F6X-N-X-LI**

Issue Date: 08/03/2023



Test Information

Test Method: LM-79-08
Report Number: P698604
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205310)
Test Lab: INNOVATION CENTER-P3
Issue Date: 08/03/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: MRI-FEU6C-30-L940 F6X-N-X-LI
Description: 6 INCH FAIL-SAFE MRI LED DOWNLIGHT WITH 4000K, 90 CRI LEDS, 6LBNLI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2425.0 lumens
Efficiency: N/A
Efficacy: 76.7 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.58
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 31.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P698604
CATALOG NUMBER: MRI-FEU6C-30-L940 F6X-N-X-LI

Luminous Intensity Polar Plot





TEST NUMBER: P698604

CATALOG NUMBER: MRI-FEU6C-30-L940 F6X-N-X-LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	96	96	96	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	91	91	89
3	105	99	94	91	103	97	93	90	95	91	89	93	90	87	90	88	86	86	86	85
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	81	81	80
5	96	88	83	79	94	87	83	79	86	82	78	84	81	78	83	80	77	77	77	76
6	92	84	79	75	90	83	78	75	82	77	74	80	76	74	79	76	73	73	73	72
7	88	80	74	71	87	79	74	71	78	73	70	77	73	70	76	72	69	69	69	68
8	84	76	71	67	83	75	70	67	74	70	67	73	69	66	73	69	66	66	66	65
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	63	63	62
10	78	69	64	61	77	69	64	61	68	64	61	67	63	60	67	63	60	60	60	59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	302673
5°	283050
10°	230846
15°	169876
20°	117085
25°	86926
30°	65295
35°	40716
40°	19766
45°	6784
50°	887
55°	669
60°	384
65°	454
70°	561
75°	0
80°	0
85°	0



TEST NUMBER: P698604
 CATALOG NUMBER: MRI-FEU6C-30-L940 F6X-N-X-LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	459.0	18.9
10°-20°	824.0	34.0
20°-30°	666.2	27.5
30°-40°	383.8	15.8
40°-50°	81.1	3.3
50°-60°	7.0	0.3
60°-70°	3.5	0.1
70°-80°	0.5	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1949.2	80.4
0°-40°	2332.9	96.2
0°-60°	2421.0	99.8
0°-90°	2425.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2425.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5521	
5°	5144	459
15°	2993	824
25°	1437	666
35°	608	384
45°	88	81
55°	7	7
65°	4	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P698604
CATALOG NUMBER: MRI-FEU6C-30-L940 F6X-N-X-LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	5521.2
2.5°	5454.8
5°	5143.6
7.5°	4696.0
10°	4147.0
12.5°	3584.1
15°	2993.2
17.5°	2423.2
20°	2007.0
22.5°	1688.9
25°	1437.1
27.5°	1223.9
30°	1031.5
32.5°	818.2
35°	608.4
37.5°	423.1
40°	276.2
42.5°	167.9
45°	87.5
47.5°	34.9
50°	10.4
52.5°	10.4
55°	7.0
57.5°	7.0
60°	3.5
62.5°	3.5
65°	3.5
67.5°	3.5
70°	3.5
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)