

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P698754

Luminaire Tested: **MRI-FEU6C-35-L930 F6X-M-X-H**

Issue Date: 08/03/2023



Test Information

Test Method: LM-79-08
Report Number: P698754
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203254)
Test Lab: INNOVATION CENTER-P3
Issue Date: 08/03/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: MRI-FEU6C-35-L930 F6X-M-X-H
Description: 6 INCH FAIL-SAFE MRI LED DOWNLIGHT WITH 3000K, 90 CRI LEDS, 6LBMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2591.0 lumens
Efficiency: N/A
Efficacy: 64.1 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 40.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P698754
CATALOG NUMBER: MRI-FEU6C-35-L930 F6X-M-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P698754

CATALOG NUMBER: MRI-FEU6C-35-L930 F6X-M-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	113	110	107	105	111	108	105	103	104	102	100		100	99	97		92
2	107	102	97	93	105	100	96	92	97	93	90		94	91	88		85
3	101	94	88	84	99	92	87	84	90	86	82		87	84	81		78
4	95	87	81	76	93	86	80	76	84	79	75		82	78	74		72
5	90	81	75	70	88	80	74	70	78	73	69		76	72	68		66
6	85	75	69	64	83	75	69	64	73	68	64		72	67	63		61
7	80	70	64	59	79	70	64	59	68	63	59		67	62	59		57
8	76	66	60	55	75	65	59	55	64	59	55		63	58	55		53
9	72	62	56	51	71	61	55	51	60	55	51		60	55	51		49
10	69	58	52	48	68	58	52	48	57	52	48		56	51	48		46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	140570
5°	138053
10°	130998
15°	122844
20°	114402
25°	105411
30°	87830
35°	61904
40°	39452
45°	23530
50°	13884
55°	8831
60°	6085
65°	4320
70°	2965
75°	2351
80°	1168
85°	0



TEST NUMBER: P698754
 CATALOG NUMBER: MRI-FEU6C-35-L930 F6X-M-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	234.5	9.0
10°-20°	606.5	23.4
20°-30°	785.9	30.3
30°-40°	583.4	22.5
40°-50°	246.3	9.5
50°-60°	87.4	3.4
60°-70°	33.7	1.3
70°-80°	11.7	0.5
80°-90°	1.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1626.9	62.8
0°-40°	2210.3	85.3
0°-60°	2544.0	98.2
0°-90°	2591.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2591.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2564	
5°	2509	234
15°	2164	607
25°	1743	786
35°	925	583
45°	304	246
55°	92	87
65°	33	34
75°	11	12
85°	0	2
90°	0	



TEST NUMBER: P698754
CATALOG NUMBER: MRI-FEU6C-35-L930 F6X-M-X-H

CANDELA DISTRIBUTION (FULL):

0°	
0°	2564.2
2.5°	2556.7
5°	2508.7
7.5°	2438.3
10°	2353.3
12.5°	2260.7
15°	2164.5
17.5°	2057.3
20°	1961.0
22.5°	1861.2
25°	1742.7
27.5°	1579.9
30°	1387.5
32.5°	1161.8
35°	925.0
37.5°	725.2
40°	551.3
42.5°	410.7
45°	303.5
47.5°	222.0
50°	162.8
52.5°	122.1
55°	92.4
57.5°	70.2
60°	55.5
62.5°	40.7
65°	33.3
67.5°	25.8
70°	18.5
72.5°	14.8
75°	11.1
77.5°	7.4
80°	3.7
82.5°	3.7
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)