

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P696644

Luminaire Tested: **MRI-FEU4C-15-L950 F4X-W-X-LI**

Issue Date: 08/03/2023



Test Information

Test Method: LM-79-08
Report Number: P696644
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)
Test Lab: INNOVATION CENTER-P3
Issue Date: 08/03/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: MRI-FEU4C-15-L950 F4X-W-X-LI
Description: 4 INCH FAIL-SAFE MRI LED DOWNLIGHT WITH 5000K, 90 CRI LEDS, 4LBWLI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1585.0 lumens
Efficiency: N/A
Efficacy: 100.3 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P696644
CATALOG NUMBER: MRI-FEU4C-15-L950 F4X-W-X-LI

Luminous Intensity Polar Plot





TEST NUMBER: P696644
 CATALOG NUMBER: MRI-FEU4C-15-L950 F4X-W-X-LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	94	94	94	92
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	86	86	86	84
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	78	78	78	77
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	72	72	72	72	70
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	65	65	65	64
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	63	60	60	60	60	58
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	55	55	55	54
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	51	51	51	49
9	69	59	52	48	68	58	52	47	57	51	47	56	51	47	55	50	47	47	47	47	45
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	43	43	43	42

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	119303
5°	121325
10°	126820
15°	134602
20°	140491
25°	139282
30°	129517
35°	110803
40°	84421
45°	49516
50°	21158
55°	6233
60°	1794
65°	1047
70°	647
75°	854
80°	0
85°	0



TEST NUMBER: P696644
 CATALOG NUMBER: MRI-FEU4C-15-L950 F4X-W-X-LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.0	6.0
10°-20°	299.7	18.9
20°-30°	467.6	29.5
30°-40°	454.9	28.7
40°-50°	227.2	14.3
50°-60°	35.2	2.2
60°-70°	4.2	0.3
70°-80°	1.2	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	862.2	54.4
0°-40°	1317.1	83.1
0°-60°	1579.5	99.7
0°-90°	1585.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1585.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	971	
5°	984	95
15°	1058	300
25°	1028	468
35°	739	455
45°	285	227
55°	29	35
65°	4	4
75°	2	1
85°	0	0
90°	0	



TEST NUMBER: P696644
CATALOG NUMBER: MRI-FEU4C-15-L950 F4X-W-X-LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	971.1
2.5°	974.8
5°	983.8
7.5°	998.4
10°	1016.6
12.5°	1040.1
15°	1058.3
17.5°	1072.8
20°	1074.6
22.5°	1061.9
25°	1027.5
27.5°	976.6
30°	913.0
32.5°	833.2
35°	738.8
37.5°	635.3
40°	526.4
42.5°	410.3
45°	285.0
47.5°	183.3
50°	110.7
52.5°	59.9
55°	29.1
57.5°	12.7
60°	7.3
62.5°	5.5
65°	3.6
67.5°	3.6
70°	1.8
72.5°	1.8
75°	1.8
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)